



7432-XX	SLIDE LENGTH	TRAVEL	* A *	* B *	* C *	* D *	RAIL LENGTH
12	11.81 [300]	12.00 [305]	8.82 [224.0]	-	-	4.00 [101.6]	10.54 [267.7]
14	13.78 [350]	13.97 [355]	8.82 [224.0]	-	-	4.00 [101.6]	10.54 [267.7]
16	15.75 [400]	15.93 [405]	12.60 [320.0]	-	-	4.00 [101.6]	13.06 [331.7]
17	16.74 [425]	16.88 [429]	12.60 [320.0]	-	-	4.00 [101.6]	13.06 [331.7]
18	17.72 [450]	17.90 [455]	13.86 [352.0]	-	-	4.00 [101.6]	13.06 [331.7]
20	19.69 [500]	19.87 [505]	12.60 [320.0]	16.38 [416.0]	-	4.00 [101.6]	16.84 [427.7]
22	21.65 [550]	21.84 [555]	13.86 [352.0]	17.64 [448.0]	18.90 [480.0]	7.00 [177.8]	20.62 [523.7]
24	23.62 [600]	23.81 [605]	15.12 [384.0]	18.90 [480.0]	-	7.00 [177.8]	20.62 [523.7]
26	25.59 [650]	25.78 [655]	15.12 [384.0]	21.42 [544.0]	-	7.00 [177.8]	24.40 [619.8]
28	27.56 [700]	27.75 [705]	16.38 [416.0]	21.42 [544.0]	23.94 [608.0]	7.00 [177.8]	24.40 [619.8]

12. AVAILABLE FOR 7432-22 ONLY.
11. SLIDE IS PROVIDED WITH PROGRESSIVE MOVEMENT.
 10. SLIDE IS PROVIDED WITH A DETENT IN THE CLOSED POSITION.
 9. SLIDE IS PROVIDED WITH SILENCING BUMPERS IN THE OPEN AND CLOSED POSITIONS.
 8. LEFT HAND SLIDE SHOWN, RIGHT HAND SLIDE OPPOSITE.
 7. HOLES OTHER THAN THOSE SHOWN MAY BE IN THE SLIDE MEMBERS AT ACCURIDE OPTION.
 6. USE ONLY M6 X 10 EURO-SCREWS OR NO.8 SLOTTED PAN OR SLOTTED BINDING HEAD SCREWS FOR MOUNTING THROUGH SLIDE MEMBERS MAX..100 HIGH X.380 DIA. SCREW HEAD CLEARANCE NECESSARY IN ORDER TO CLEAR TRAVERSING INTERMEDIATE MEMBER.
 5. WIDTH OF SLIDE IS MEASURED IN THE CLOSED POSITION, ACROSS THE AREA WHERE THE SLIDE MEMBERS ARE FULLY ENGAGED WITH BALL BEARINGS.
 4. FINISH: ELECTRO -ZINC PLATED, CHROMATE COATED.
("C" = CLEAR AND "CB" = BLACK)
 3. LUBRICANT: HIGH-LOW TEMPERATURE GREASE.
 2. BALL BEARINGS: CARBURIZED STEEL.
 1. MATERIAL: SLIDE MEMBERS AND COMPONENT PARTS WORK HARDENED COLD ROLLED STEEL

NOTES: UNLESS OTHERWISE SPECIFIED.

SYM.	IS	DESCRIPTION	WAS	DATE	APPD.
REVISIONS					

THIS **Accuride** PRODUCT COVERED BY U.S. PATENTS #3205025, #3778120 AND OTHER U.S. PATENTS PENDING.

CUSTOMER: ACCURIDE

P/N: _____ REV. _____

SCALE: N.T.S. DATE: 01-08-97 CONTROLLING DOCUMENT: ACCURIDE □ CUSTOMER

TOLERANCES NOT SHOWN: in mm .xxx ± .010 .25 Travel ± .13 3.3 in .xx ± .030 .76 Holes ± .006 .15 Angular ± 1°

PART NUMBER: 4 7432-12/28-L/R REV. _____

THIS DOCUMENT IS FURNISHED FOR THE EXPRESS AND EXCLUSIVE PURPOSE OF CONVEYING INFORMATION TO CUSTOMERS AND SUPPLIERS OF ACCURIDE INTERNATIONAL INC., AND IS NOT TO BE DISCLOSED TO COMPETITIVE SOURCES.