



- 11 STEEL STAMP LEFT HAND AS SHOWN, RIGHT HAND OPPOSITE.
- SLIDE IS PROVIDED WITH A DETENT IN THE CLOSED POSITION PULL FORCE 2-5 Lbs.
 - SLIDE IS PROVIDED WITH SILENCING BUMPERS IN OPEN AND CLOSED POSITIONS.
 - SLIDE ASSEMBLY IS UNHANDED, ADAPTER BRACKET IS HANDED.
 - HOLES OTHER THAN SHOWN MAY BE IN THE MEMBERS AT ACCURIDE OPTION.
 - USE ONLY No.8 SLOTTED PAN OR SLOTTED BINDING HEAD SCREWS FOR MOUNTING THROUGH SLIDE MEMBERS. MAX. .100 HIGH X .380 DIAMETER SCREW HEAD CLEARANCE NECESSARY IN ORDER TO CLEAR TRAVERSING BALL RETAINER.
 - WIDTH OF SLIDE MEASURED IN CLOSED POSITION, ACROSS THE AREA WHERE THE SLIDE MEMBERS ARE FULLY ENGAGED WITH BALL BEARINGS
 - FINISH : ELECTRO-ZINC PLATE, CHROMATE COATED.
 - LUBRICANT: HIGH-LOW TEMPERATURE GREASE.
 - BALL BEARING : CARBURIZED STEEL.
 - MATERIAL : SLIDE MEMBERS AND COMPONENT PARTS : WORK HARDENED COLD ROLLED STEEL.

NOTES: UNLESS OTHERWISE SPECIFIED

DRAWER MEMBER ADAPTER

PART NO.	SLIDE LENGTH	H	J	K
5430-1216	3640-12/-16	10.00	-	8.50
5430-1720	3640-17/-20	12.00	-	10.50
5430-2124	3640-21/-24	14.00	7.00	12.50
5430-2528	3640-25/-28	17.00	8.50	15.50

SLIDE ASSEMBLY

SLIDE LENGTH	SLIDE TRAVEL	LOAD RATING	A	B	C	D	E	F	G
12.00	13.00	225	----	5.33	7.05	8.05	9.05	1.00	8.50
13.00	14.00	221	----	6.33	8.05	9.05	10.05	1.00	8.50
14.00	15.00	219	----	7.33	9.05	10.05	11.05	1.00	8.50
15.00	16.00	215	----	8.33	10.05	11.05	12.05	1.00	8.50
16.00	17.00	212	----	9.33	11.05	12.05	13.05	1.00	8.50
17.00	18.00	209	----	10.33	12.05	13.05	14.05	1.50	10.50
18.00	19.00	205	7.50	11.33	13.05	14.05	15.05	1.50	10.50
19.00	20.00	201	8.00	12.33	14.05	15.05	16.05	1.50	10.50
20.00	21.00	197	8.50	13.33	15.05	16.05	17.05	1.50	10.50
21.00	22.00	192	9.00	14.33	16.05	17.05	18.05	2.00	12.50
22.00	23.00	189	9.50	15.33	17.05	18.05	19.05	2.00	12.50
23.00	24.00	185	10.00	16.33	18.05	19.05	20.05	2.00	12.50
24.00	25.00	180	10.50	17.33	19.05	20.05	21.05	2.00	12.50
25.00	26.00	175	11.00	18.33	20.05	21.05	22.05	2.50	15.50
26.00	27.00	169	11.50	19.33	21.05	22.05	23.05	2.50	15.50
27.00	28.00	160	12.00	20.33	22.05	23.05	24.05	2.50	15.50
28.00	29.00	149	12.50	21.33	23.05	24.05	25.05	2.50	15.50

THIS Accuride PRODUCT COVERED BY U.S. PATENTS #3205025, #3778120 AND OTHER U.S. PATENTS PENDING.

CUSTOMER: ACCURIDE		REV.			
P/N:		REV.			
SCALE N.T.S.	DATE	CONTROLLING DOCUMENT		PART NUMBER	
DRAWN		<input checked="" type="checkbox"/> ACCURIDE <input type="checkbox"/> CUSTOMER			
APPROVED		TOLERANCES NOT SHOWN		REV.	
		in mm .xxx ± .010 .25 Travel ± .13 3.3 .xx ± .030 .76 Holes ± .006 .15 Angular ± 1°		C 3640-STD	

THIS DOCUMENT IS FURNISHED FOR THE EXPRESS AND EXCLUSIVE PURPOSE OF CONVEYING INFORMATION TO CUSTOMERS AND SUPPLIERS OF ACCURIDE INTERNATIONAL INC., AND IS NOT TO BE DISCLOSED TO COMPETITIVE SOURCES.

SYM.	IS	DESCRIPTION	WAS	DATE	APPD.
REVISIONS					