



SEE SHEET 2 FOR LENGTHS OVER 28

PART NO.	LENGTH	A	B	C	D	E	F	G	H	J	K	M	N	P	Q	R
-10	10.00 [254.0]	---	---	---	---	---	4.06 [103.1]	5.06 [128.5]	5.81 [147.6]	6.56 [166.6]	---	---	---	6.00 [152.4]	8.25 [209.6]	9.00 [228.6]
-12	12.00 [304.8]	---	---	---	---	---	6.06 [153.9]	7.06 [179.3]	7.81 [198.4]	8.56 [217.4]	---	---	---	8.00 [203.2]	10.25 [260.4]	11.00 [279.4]
-14	14.00 [355.6]	---	---	---	---	---	8.06 [204.7]	9.06 [230.1]	9.81 [249.2]	10.56 [268.2]	---	---	---	10.00 [254.0]	12.25 [311.2]	13.00 [330.2]
-15	15.00 [381.0]	5.00 [127.0]	---	---	---	---	9.06 [230.1]	10.06 [255.5]	10.81 [274.6]	11.56 [293.6]	---	---	---	11.00 [279.4]	13.25 [336.6]	14.00 [355.6]
-16	16.00 [406.4]	5.00 [127.0]	---	---	---	---	10.06 [255.5]	11.06 [280.9]	11.81 [300.0]	12.56 [319.0]	---	---	---	12.00 [304.8]	14.25 [362.0]	15.00 [381.0]
-18	18.00 [457.2]	5.00 [127.0]	---	---	---	9.69 [246.1]	12.06 [306.3]	13.06 [331.7]	13.81 [350.8]	14.56 [369.8]	---	---	---	14.00 [355.6]	16.25 [412.8]	17.00 [431.8]
-20	20.00 [508.0]	5.00 [127.0]	7.50 [190.5]	---	---	11.69 [296.9]	14.06 [357.1]	15.06 [382.5]	15.81 [401.6]	16.56 [420.6]	---	---	---	16.00 [406.4]	18.25 [463.6]	19.00 [482.6]
-22	22.00 [558.8]	5.00 [127.0]	7.50 [190.5]	---	---	13.69 [347.7]	16.06 [407.9]	17.06 [433.3]	17.81 [452.4]	18.56 [471.4]	---	---	---	18.00 [457.2]	20.25 [514.4]	21.00 [533.4]
-24	24.00 [609.6]	5.00 [127.0]	7.50 [190.5]	---	---	15.69 [398.5]	18.06 [458.7]	19.06 [484.1]	19.81 [503.2]	20.56 [522.2]	---	---	---	20.00 [508.0]	22.25 [565.2]	23.00 [584.2]
-26	26.00 [660.4]	5.00 [127.0]	7.50 [190.5]	---	---	17.69 [449.3]	20.06 [509.5]	21.06 [534.9]	21.81 [554.0]	22.56 [573.0]	---	---	---	22.00 [558.8]	24.25 [616.0]	25.00 [635.0]
-28	28.00 [711.2]	5.00 [127.0]	7.50 [190.5]	---	---	19.69 [500.1]	22.06 [560.3]	23.06 [585.7]	23.81 [604.8]	24.56 [623.8]	---	---	---	24.00 [609.6]	26.25 [666.8]	27.00 [685.8]

- USE 1/4 INCH [M6] HEX-HEAD SCREWS WITH .260 HOLES OR #10 [M5] HEX-HEAD SCREWS WITH .203 HOLES FOR MOUNTING THROUGH SLIDE MEMBERS. MAXIMUM SCREW HEAD OF .190 HIGH X .475 DIAMETER NECESSARY TO CLEAR TRAVERSING MEMBERS.
- WIDTH OF SLIDE MEASURED IN CLOSED POSITION, ACROSS THE AREA WHERE THE SLIDE MEMBERS ARE FULLY ENGAGED WITH BALL BEARINGS.
- FINISH: ELECTRO-ZINC PLATED, CHROMATE COATED. "C" FOR CLEAR; "CB" FOR BLACK.
- LUBRICANT: HIGH-LOW TEMPERATURE GREASE.
- BALL BEARINGS: CARBURIZED STEEL.
- MATERIAL: SLIDE MEMBERS AND COMPONENT PARTS: WORK-HARDENED, COLD-ROLLED STEEL.
- 9301-44 PACKAGED IN BULK CONTAINER ONLY.
- SLIDE IS PROVIDED WITH A SILENCING BUMPER IN THE CLOSED POSITION.
- HOLES OTHER THAN THOSE SHOWN MAY BE IN THE MEMBERS AT ACCURIDE OPTION.

SYM.	IS	DESCRIPTION	WAS	DATE	APPD.
A		ADDED INT. MEMBER HAT SECTION .203 & .260 DM HOLES .203 .203 & .260 CM HOLES FOR 10X82" REVISED NOTE 6		01-11-02	JAG
-		NOTE #4: ADDED "CB" FOR BLACK		06-27-01	TPD
-		ADDED SHEET 2, ADDED NOTE #9 ADDED LENGTH: 10, 15, 40, 42 & 44 ADDED CLOSED POSITION VIEW		03-13-01	TPD
-		REDRAWN FOR CLARITY		01-05-99	JAG

1. MATERIAL: SLIDE MEMBERS AND COMPONENT PARTS: WORK-HARDENED, COLD-ROLLED STEEL.
2. BALL BEARINGS: CARBURIZED STEEL.
3. LUBRICANT: HIGH-LOW TEMPERATURE GREASE.
4. FINISH: ELECTRO-ZINC PLATED, CHROMATE COATED. "C" FOR CLEAR; "CB" FOR BLACK.
5. WIDTH OF SLIDE MEASURED IN CLOSED POSITION, ACROSS THE AREA WHERE THE SLIDE MEMBERS ARE FULLY ENGAGED WITH BALL BEARINGS.
6. USE 1/4 INCH [M6] HEX-HEAD SCREWS WITH .260 HOLES OR #10 [M5] HEX-HEAD SCREWS WITH .203 HOLES FOR MOUNTING THROUGH SLIDE MEMBERS. MAXIMUM SCREW HEAD OF .190 HIGH X .475 DIAMETER NECESSARY TO CLEAR TRAVERSING MEMBERS.

NOTES: UNLESS OTHERWISE SPECIFIED

THIS *Accuride* PRODUCT COVERED BY U.S. PATENTS #3205025, #3778120 AND OTHER U.S. PATENTS PENDING.

CUSTOMER: ACCURIDE

P/N: _____ REV. _____

SCALE: N.T.S. DATE: 03-05-98 CONTROLLING DOCUMENT: ACCURIDE CUSTOMER

TOLERANCES NOT SHOWN: .xxx ± .010 .25 in .13 mm, .xx ± .030 .76 in .33 mm, Travel ± .13 in .33 mm, Holes ± .006 .15 in, Angular ± 1°

3-MEMBER, BALL BEARING HEAVY-DUTY SLIDE

PART NUMBER: 9301-10/60 REV. A

THIS DOCUMENT IS FURNISHED FOR THE EXPRESS AND EXCLUSIVE PURPOSE OF CONVEYING INFORMATION TO CUSTOMERS AND SUPPLIERS OF ACCURIDE INTERNATIONAL INC., AND IS NOT TO BE DISCLOSED TO COMPETITIVE SOURCES.