




CFC


POSITIVE INDIRECT SYSTEM GAS TWO HEATER SYSTEM



NOTES:

- 1 AIR CURTAIN MUST BE INSTALLED SO AIR STREAM IS NOT OBSTRUCTED WHEN DEFLECTED 20° TO EITHER SIDE OF C. L.
- 2 ELECTRICAL CONNECTIONS TO BE FLEXIBLE.
- 3 FIELD VERIFY DIMENSIONS.
- 4 ANCHORS TO SUPPORTING STRUCTURE BY OTHERS.
- 5 ADEQUACY OF SUPPORTING STRUCTURE IS TO BE VERIFIED BY A PROFESSIONAL STRUCTURAL ENGINEER.
- 6 SUPPLY PRESSURES HIGHER THAN 0.50 POUND REQUIRE INSTALLATION OF AN ADDITIONAL SERVICE REGULATOR EXTERNAL TO THE UNIT.
- 7 OPTIONAL CONTROL PANEL AVAILABLE: LEFT HAND MOUNT, RIGHT HAND MOUNT, & REMOTE. PLEASE SPECIFY.
- 8 DIMENSIONS IN INCHES.

END VIEW



CAUTION:

HEATER IS EQUIPPED FOR A MAXIMUM GAS SUPPLY PRESSURE OF 1/2 POUND, 8 OUNCES, OR 14 INCHES WATER COLUMN.

MODEL	NOZZLE WIDTH "A"	MOUNTING WIDTH "B"	UNIT WIDTH "C"	MBTU INPUT	WIDTH "D"	WIDTH "E"	WIDTH "F"	DEPTH "G"	DEPTH "H"	DEPTH "I"	FLUE "J"	WIDTH "K"	WIDTH "L"
CFC-1-96G	96.00	97.50	99.00	2 @ 230	4.688	40.125	17.00	3.688	40.00	93.750	5.00	3.50	7.874
CFC-1-120G	117.00	118.50	120.00	2 @ 345	9.938	40.125	17.00	3.688	41.125	94.875	6.00	3.50	18.375
CFC-1-144G	144.00	145.50	147.00	2 @ 400	16.688	40.125	21.625	3.688	41.125	94.875	6.00	3.50	31.874

PROJECT		
LOCATION		
ARCHITECT		
ENGINEER		
DWG. NO.	CFCK3046	TITLE: BERNER
DATE	05JUL01	MODEL CFC AIR CURTAIN
BY	B. Peffer	INDIRECT GAS FIRED - TWO HEATER SYSTEM
REPLACES	17JAN00	
BY	B. Peffer	BERNER INTERNATIONAL CORP. NEW CASTLE, PA.