



- 11 MOUNTING HOLES AVAILABLE FOR C 3132-26SC-L/R AND C 3132-28SC-L/R SLIDES ONLY.
10. SLIDE IS PROVIDED WITH A SELF CLOSING FEATURE.
9. SLIDE IS PROVIDED WITH SILENCING FEATURES IN THE OPEN AND CLOSED POSITIONS
8. LEFT-HAND SLIDE SHOWN, RIGHT-HAND SLIDE OPPOSITE.
7. HOLES OTHER THAN THOSE SHOWN MAY BE IN THE MEMBERS AT ACCURIDE OPTION.
6. FOR SLIDE MOUNTING, USE #8 X 5/8" [15.8] PHILLIPS FLAT HEAD SCREWS.
5. WIDTH OF SLIDE IS MEASURED IN CLOSED POSITION, ACROSS THE AREA WHERE THE SLIDE MEMBERS ARE FULLY ENGAGED WITH BALL BEARINGS.
4. FINISH: ELECTRO-ZINC PLATED.
3. LUBRICANT: HIGH-LOW TEMPERATURE GREASE.
2. POLYMER ROLLERS IN DRAWER AND CABINET MEMBERS. POLYMER BALL BEARINGS IN DRAWER MEMBER. CARBURIZED BALL BEARINGS IN CABINET MEMBERS.
1. MATERIAL: SLIDE MEMBERS AND COMPONENT PARTS: WORK-HARDENED, COLD-ROLLED STEEL.
- NOTES: UNLESS OTHERWISE SPECIFIED

PART NUMBER	SLIDE LENGTH	SLIDE TRAVEL	A	B	DRAWER DEPTHS	CABINET DEPTHS
C 3132-28SC-L/R	12.00 (304.8)	11.50 (292.1)	5.04 (128.0)	3.78 (96.0)	12.00 (304.8)	12.83 TO 14.83 (320.8) (371.6)
C 3132-48SC-L/R	14.00 (355.6)	13.50 (342.9)	5.04 (128.0)	3.78 (96.0)	14.00 (355.6)	14.83 TO 16.83 (371.6) (422.4)
C 3132-68SC-L/R	16.00 (406.4)	15.50 (393.7)	5.04 (128.0)	7.56 (192.0)	16.00 (406.4)	16.83 TO 18.83 (422.4) (473.2)
C 3132-88SC-L/R	18.00 (457.2)	17.50 (444.5)	5.04 (128.0)	7.56 (192.0)	18.00 (457.2)	18.83 TO 20.83 (473.2) (524.0)
C 3132-20SC-L/R	20.00 (508.0)	18.50 (465.3)	8.82 (224.0)	7.56 (192.0)	20.00 (508.0)	20.83 TO 22.83 (524.0) (574.8)
C 3132-22SC-L/R	22.00 (558.8)	21.50 (546.1)	8.82 (224.0)	10.08 (256.0)	22.00 (558.8)	22.83 TO 24.83 (574.8) (625.6)
C 3132-24SC-L/R	24.00 (609.6)	23.50 (596.8)	8.82 (224.0)	10.08 (256.0)	24.00 (609.6)	24.83 TO 26.83 (625.6) (676.4)
C 3132-26SC-L/R	26.00 (660.4)	25.50 (647.7)	8.82 (224.0)	10.08 (256.0)	26.00 (660.4)	26.83 TO 28.83 (676.4) (727.2)
C 3132-28SC-L/R	28.00 (711.2)	27.50 (698.5)	8.82 (224.0)	10.08 (256.0)	28.00 (711.2)	28.83 TO 30.83 (727.2) (778.0)

Accuride

N.T.S.

FLOPEZ 10/7/05

X

3 MEMBER SLIDE

C 3132-12SC/-28SC

*