

SPECIFICATIONS:

DOORS SHOWN AS FLEXIBLE VINYL IMPACT TRAFFIC DOORS, DOUBLE ACTING, SHALL BE MODEL 200 DOORS AS MANUFACTURED BY CHASE INDUSTRIES, INC., CINCINNATI, OHIO, TO FIT DOOR OPENING _____ WIDE BY _____ HIGH.

VISION PANELS TO BE CONSTRUCTED OF .160 CLEAR USDA FLEXIBLE PVC MATERIAL, INSTALLED ON THE EDGE OF THE DOOR PANEL.


- 15"x14" (STANDARD) AT 60" ON CENTER
- 22"x22" (OPTIONAL) AT 64" ON CENTER

DOOR SHALL BE CONSTRUCTED OF TWO LAYERS OF .117 TEXTURED PVC (USDA APPROVED) WITH ANTI-ABRASION SURFACE, LAMINATED BACK-TO-BACK. BRACKET POCKET, BALLOON JAMB SEALS, AND TOP AND BOTTOM WIPER SEALS ARE TWO-PLY VINYL COATED NYLON. THE EDGES ARE HEAT SEALED TOGETHER.

VALANCE OPTION:
 WHEN HEIGHT IS LESS THAN 6".
 CONSTRUCTED OF 2-PLY VINYL COATED NYLON ATTACHED TO .080 x 1 x 1 KYDEX ANGLE OF COLOR THAT MATCHES DOOR.
 WHEN HEIGHT IS MORE THAN 6".
 CONSTRUCTED OF 2 LAYERS OF .117 PVC ATTACHED TO 1/8" x 1 x 1 ALUMINUM ANGLE ON BOTH SIDES.

- (SPECIFY COLOR:) FOREST GREEN GRAY
- CHOCOLATE RED MEDIUM BROWN
- NAVY ROYAL BLUE BLACK

DOOR TO UTILIZE TOP MOUNTED GRAVITY-OPERATED HINGING SYSTEM, COMPLETE WITH 1/2" THICK ZINC WALL BRACKET WITH BEARINGS AND 5/8" DIAMETER STEEL ROD ARM.



- OPTIONAL 100CRB HINGE

MODEL # 200, AIRGARD BIPARTING FLEXIBLE VINYL IMPACT TRAFFIC DOOR

@COPYRIGHT 2000 CHASE INDUSTRIES, INC. SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. 1 800-543-4455 www.chasedoors.com

CUSTOMER INFORMATION:

DATE: 8/03/00	CHASE APPROVAL	REV.
FORM #	SD4115	