

SIDE VIEW - 973

SPECIFICATIONS:

DOORS SHOWN AS FLEXIBLE RETAIL VINYL TRAFFIC DOORS, DOUBLE ACTING, SHALL BE MODEL 973 DOORS AS MANUFACTURED BY CHASE INDUSTRIES, INC., CINCINNATI, OHIO, TO FIT DOOR OPENING _____ WIDE BY _____ HIGH.


DOOR SHALL BE CONSTRUCTED OF .160 THICK PVC (CLEAR) WITH A TWO-PLY VINYL COATED NYLON BRACKET POCKET, BALLOON JAMB SEALS, AND TOP AND BOTTOM WIPER SEALS. USDA APPROVED TEXTURED VINYL IMPACT PLATES (.117) ON BOTH SIDES OF DOOR PANEL.
 (SPECIFY COLOR:) FOREST GREEN GRAY
 CHOCOLATE RED MEDIUM BROWN
 NAVY ROYAL BLUE BLACK

DOOR TO UTILIZE TOP MOUNTED GRAVITY-OPERATED HINGING SYSTEM, COMPLETE WITH 1/2" THICK ZINC WALL BRACKET WITH BEARINGS AND 5/8" DIAMETER STEEL ROD ARM.

OPTIONAL 100CRB HINGE

VISION PANELS TO BE CONSTRUCTED OF .160 CLEAR USDA FLEXIBLE PVC MATERIAL.

VALANCE OPTION:
 CONSTRUCTED OF 2-PLY VINYL COATED NYLON ATTACHED TO .080 x 1 x 1 KYDEX ANGLE OF COLOR THAT MATCHES DOOR.
 WHEN HEIGHT IS MORE THAN 6", .120 VINYL WEIGHTS ARE ADDED TO VALANCE.



TOP MOUNTED GRAVITY HINGE

MODEL # 973, AIRGARD BIPARTING, w/ TEXTURED VINYL IMPACT PLATES, FLEXIBLE VINYL TRAFFIC DOOR

@COPYRIGHT 2000
 CHASE INDUSTRIES, INC.
 SPECIFICATIONS SUBJECT TO
 CHANGE WITHOUT NOTICE.
 1 800-543-4455
 www.chasedoors.com

CUSTOMER INFORMATION:

DATE: 7/31/00	CHASE APPROVAL	REV.
FORM #	SD4001	