


ASSA ABLOY Entrance Systems
1900 Airport Road
Monroe, NC 28110
Phone: 1-866-237-2687
specdesk.na.besam@assaabloy.com

DOOR SYSTEM coDoor




 $\langle \rangle$

& 2-POINT LOCK. OPTIONAL 5 OR 3 POSITION SWITCH (OFF-EXIT ONLY-AUTO-REDUCED OPENING-HOLD OPEN OR, OFF. AUTO, HOLD OPEN), MOTION/PRESENCE SENSORS, THE AUTOMATIC OPERATOR & WEATHERSTRIP, FRAMES, DOORS & SIDELITES WITH VERTICAL WEATHERSTRIP, EMERGENCY BREAKAWAY NOTE: STD CLASS 1 ANODIZED FINISH: CLEAR- AA-M12C22A31, .010 MM. THE STANDARD PACKAGE CONSISTS OF: DARK BRONZE- AA-M12C22A44, .018 MM.

SPECIAL FINISHES ARE AVAILABLE. THIS PACKAGE WILL ACCEPT UP TO 1" (25.4) INSULATED GLASS

BESAM SL500 ECODOOR OPTIONS (CHOOSE ANY OF THE FOLLOWING): ECODOOR SEALS WITH CONCEALED SWEEPS, MAGNETIC CATCHES, HYDRAULIC CLOSERS WITH MAGNETIC CATCHES

ECO SEALS EXCEED ASTM E283 REQUIREMENTS BY REDUCING AIR FLOW BY APPROXIMATLY 40%.



BU

SWEEPS (OPTION)
REQUIRED FOR ASTM E283
AND ECO PACKAGE

DRN BY CLW DATE 3/21/1	DWG NO. 1010545
3 CHK BY_	
DATE_	
REV.3.0 DATE 8/31/	
	DRN BY CLW DATE 3/21/13 CHK BY_ DATE_ REV 3.0 DATE 8/31/16