



SPECIFICATIONS:

DOORS SHOWN AS SOLID CORE STYLE SERVICE DOORS, DOUBLE ACTING, SHALL BE MODEL SC-3000 DOORS AS MANUFACTURED BY CHASE INDUSTRIES, INC., CINCINNATI, OHIO, TO FIT DOOR OPENING _____ WIDE BY _____ HIGH.

DOOR SHALL BE CONSTRUCTED OF 3/4" THICK 7-PLY PLYWOOD CORE WITH .032" THICK ANODIZED ALUMINUM CLADDING, BOTH SIDES. THE PERIMETER EDGES TO BE 18 GAUGE STAINLESS STEEL EDGE TRIM.

COMPLETE WITH CHASE GRAVITY-OPERATED HINGING SYSTEM WITH HARDENED STEEL CAM AND ROLLER. BOTTOM HINGE PIN TO BE 1/2" DIAMETER STEEL MOUNTED TO 3/16" THICK STEEL ANGLE. TOP AND BOTTOM HINGES SHALL MOUNT DIRECTLY THROUGH DOOR BODY.

OPTIONAL "E" SERIES HINGE

ACRYLIC VISION PANEL TO BE 1/4" TH. x 9" x 14" SET IN BLACK RUBBER MOLDING (STD).

- INCLUDE OPTIONS AS INDICATED BELOW:
- 3-3/4"x8-3/4" HIGH ALUM. JAMB GUARDS
 - 3-3/4"x12" HIGH ALUMINUM JAMB GUARDS
 - 3-3/4"x18" HIGH ALUMINUM JAMB GUARDS

- IMPACT PLATE (BOTH SIDES): YES NO
- STAINLESS STEEL IMPACT PLATES (STANDARD)
 - STAINLESS STEEL/GALVANIZED IMPACT PLATES
 - GALVANIZED IMPACT PLATES
 - PLASTIC IMPACT PLATES (SPECIFY COLOR): FOREST GREEN JADE CADET BLUE WHITE GRAY CLOUD GRAY CHOCOLATE RED MEDIUM BROWN NAVY ROYAL BLUE BLACK BEIGE BURGUNDY
- IMPACT PLATE HEIGHT: 12" 18" 24" 36" 48"

- BUMPER OPTIONS (BOTH SIDES): YES NO
- STANDARD TEARDROP CROSS-LINKED POLYETHYLENE (SPECIFY COLOR) _____ (AND HEIGHT) _____
 - PVC STRIP (SPECIFY COLOR) _____ ALUM. STRIP (SPECIFY LOCATION) _____

MODEL # SC-3000, NON-GASKETED BIPARTING SOLID CORE STYLE RETAIL SERVICE DOOR

@COPYRIGHT 2000 CHASE INDUSTRIES, INC. SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. 1 800-543-4455 www.chasedoors.com

CUSTOMER INFORMATION:

DATE: 6/2/00	CHASE APPROVAL
FORM # SD4030	REV. C