



**SPECIFICATIONS:**

DOORS SHOWN AS SOLID CORE STYLE SERVICE DOORS, DOUBLE ACTING, SHALL BE MODEL SC-3002G DOORS AS MANUFACTURED BY CHASE INDUSTRIES, INC., CINCINNATI, OHIO, TO FIT DOOR OPENING \_\_\_\_\_ WIDE BY \_\_\_\_\_ HIGH.

DOORS SHALL BE CONSTRUCTED OF 3/4" THICK 7-PLY PLYWOOD CORE WITH HIGH PRESSURE LAMINATE, BOTH SIDES. ALL PERIMETER EDGES AND HINGE LOCATIONS TO BE FULLY GASKETED.

SPECIFY COLOR AND NUMBER OF LAMINATE:

COMPLETE WITH CHASE GRAVITY-OPERATED HINGING SYSTEM WITH HARDENED STEEL CAM AND ROLLER. BOTTOM HINGE PIN TO BE 1/2" DIAMETER STEEL MOUNTED TO 3/16" THICK STEEL ANGLE. TOP AND BOTTOM HINGES SHALL MOUNT DIRECTLY THROUGH DOOR BODY.

OPTIONAL "E" SERIES HINGE (NOT GASKETED)

ACRYLIC VISION PANEL TO BE 1/4" TH. x 9" x 14" SET IN BLACK RUBBER MOLDING (STD).

INCLUDE OPTIONS AS INDICATED BELOW:

- 3-3/4"x8-3/4" HIGH ALUM. JAMB GUARDS
- 3-3/4"x12" HIGH ALUMINUM JAMB GUARDS
- 3-3/4"x18" HIGH ALUMINUM JAMB GUARDS

IMPACT PLATE (BOTH SIDES):  YES  NO  
 STAINLESS STEEL IMPACT PLATES (STANDARD)  
 STAINLESS STEEL/GALVANIZED IMPACT PLATES  
 GALVANIZED IMPACT PLATES  
 PLASTIC IMPACT PLATES

(SPECIFY COLOR:)  
 FOREST GREEN  JADE  
 CADET BLUE  WHITE  GRAY  CLOUD GRAY  
 CHOCOLATE  RED  MEDIUM BROWN  NAVY  
 ROYAL BLUE  BLACK  BEIGE  BURGUNDY

IMPACT PLATE HEIGHT:  
 12"  18"  24"  36"  48"

BUMPER OPTIONS (BOTH SIDES):  YES  NO  
 STANDARD TEARDROP CROSS-LINKED POLYETHYLENE (SPECIFY COLOR) \_\_\_\_\_ (AND HEIGHT) \_\_\_\_\_  
 PVC STRIP (SPECIFY COLOR) \_\_\_\_\_  ALUM. STRIP (SPECIFY LOCATION) \_\_\_\_\_

MODEL # SC-3002G, BIPARTING  
 SOLID CORE STYLE RETAIL SERVICE DOORS

@COPYRIGHT 2000  
 CHASE INDUSTRIES, INC.  
 SPECIFICATIONS SUBJECT TO  
 CHANGE WITHOUT NOTICE.  
 1 800-543-4455  
 www.chasedoors.com

CUSTOMER INFORMATION:

DATE: 6/27/00 CHASE APPROVAL

FORM # SD4137

REV.  
 A