



UNREINFORCED MEMBRANE T-JOINT PATCHES

EVERGUARD® 8" REINFORCED UTILITY MEMBRANE FLASHING

HEAT WELDED LAP

EVERGUARD® REINFORCED MEMBRANE SHEET

ENERGYGUARD™ ROOF INSULATION

ROOF DECK/SUBSTRATE

**NOTE:**

1. FOR INSULATION THICKNESS GREATER THAN 8" CONTACT GAF CONTRACTOR SERVICES FOR ALTERNATE ATTACHMENT REQUIREMENTS.
2. FOR HEAT WELDING LAPS USE 1 1/2" WELD WITH MACHINE ROBOT WELDER AND 2" WELD WITH HAND WELDER.
3. APPLY EVERGUARD® TPO CUT EDGE SEALANT TO ALL CUT REINFORCED TPO EDGES ( REFER TO DETAIL MA/FA/BA 115 ).



**COVER STRIP END LAP  
FLEECE BACK MEMBRANE**

DRAWING #  
**MA/FA/BA 103**

SCALE  
N.T.S.

ISSUE/ REVISION DATE  
11-01-06