



**NOTE#1:** Wood furring strips to be Southern Pine PT 1"x3" nominal @ 16" o.c.

**NOTE#2:** Screw types  
 ITW Buildex screws, stainless steel  
 Wood screws, hot dipped galv.  
 Sheet metal screws, stainless steel.  
 Screw head to be for wood or metal only.  
 (see attached documentation for shear and pullout test results)

**NOTE#3:** Panel adhesive to be Liquid Nails, heavy duty construction, LN901, applied to furring strips, 3" diameter, 3/8" thick, every 16" o.c.

**NOTE#4:** Masonry Anchor type:  
 Model: PF3-134 ITW Ramset Red Head, 3/16" x 1 3/4", with 1 1/4" embedment @ 6" from top & bottom, and 12" o.c.

**TYPICAL SILL DETAIL**  
**EXTRUSIONS ON BLOCK OR CONCRETE**