

MARK	STANDARD MODEL NUMBER	NO. REQ'D	LENGTH	WEIGHT (LBS)	MOTOR FAN DATA								REMARKS		
					MOTOR HP	MOTOR RPM	VOLTS & PHASE	FLA (AMPACITY) SINGLE PHASE		FLA (AMPACITY) THREE PHASE		Max FPM at Nozzle		Max CFM at Nozzle	dBA Measured 10 ft. from Nozzle
								115V	208V 240V	208V 240V	460V				
	36		3'	75	1/2	1750		5.1 (6.4)	2.5 (3.2)	1.8 (2.3)	0.8 (1.0)	3400	2550	66	
	42		3' 6"	80	1/2	1750		5.1 (6.4)	2.5 (3.2)	1.8 (2.3)	0.8 (1.0)	2925	2550	66	
	48		4'	90	1/2	1750		5.1 (6.4)	2.5 (3.2)	1.8 (2.3)	0.8 (1.0)	2550	2550	66	
	64-2		5' 4"	125	Two 1/2	1750		10.2 (12.8)	5.1 (6.4)	3.6 (4.5)	1.6 (2.0)	3200	5100	68	
	72-2		6'	135	Two 1/2	1750		10.2 (12.8)	5.1 (6.4)	3.6 (4.5)	1.6 (2.0)	3475	5100	68	
	78-2		6' 6"	145	Two 1/2	1750		10.2 (12.8)	5.1 (6.4)	3.6 (4.5)	1.6 (2.0)	3200	5100	68	
	84-2		7'	150	Two 1/2	1750		10.2 (12.8)	5.1 (6.4)	3.6 (4.5)	1.6 (2.0)	2925	5100	68	
	96-2		8'	160	Two 1/2	1750		10.2 (12.8)	5.1 (6.4)	3.6 (4.5)	1.6 (2.0)	2550	5100	68	
	96-3		8'	190	Three 1/2	1750		15.3 (19.2)	7.5 (9.4)	5.4 (6.9)	2.4 (3.0)	3825	7650	71	
	108-2		9'	195	Two 1/2	1750		10.2 (12.8)	5.1 (6.4)	3.6 (4.5)	1.6 (2.0)	2550	5100	71	
	108-3		9'	210	Three 1/2	1750		15.3 (19.2)	7.5 (9.4)	5.4 (6.9)	2.4 (3.0)	3450	7650	71	
	120-3		10'	220	Three 1/2	1750		15.3 (19.2)	7.5 (9.4)	5.4 (6.9)	2.4 (3.0)	3060	7650	71	
	144-3		12'	240	Three 1/2	1750		15.3 (19.2)	7.5 (9.4)	5.4 (6.9)	2.4 (3.0)	2550	7650	71	
	144-4		12'	280	Four 1/2	1750		20.4 (25.6)	10.2 (12.8)	7.2 (9.0)	3.2 (4.0)	3400	10,200	73	

**EQUIPMENT SPECIFICATIONS - Standard Features**

**GENERAL**  
 Air curtain shall be a Mars® Air Doors brand air curtain: Type Standard Unheated.

**APPROVALS**  
 Air curtain shall be Underwriters Laboratories Listed and meet the requirements of the National Electric Code.

**CABINET**  
 Cabinet shall be a self contained one piece housing with sufficient strength for fastening to wall on both ends without intermediate support. Cabinet constructed of fire retardant, corrosion proof paint lock metal and double protected with gray baked rust preventative electrostatic polyurethane powder coating. Cabinet to have mechanically field adjustable variable intake louver assembly capable of reducing outlet air velocity up to 60% with louver in totally closed position. Discharge air outlet nozzle shall be wedge shaped containing adjustable air directional vanes with 40° sweep front to back. Motor/Fan assembly to be easily accessible for maintenance.

**MOTORS AND BLOWER WHEELS**  
 Motor(s) shall be totally enclosed air over (TEAO) type suitable for continuous heavy duty, all angle operation. Construction shall include sealed lifetime pre-lubricated ball bearings, resilient mounted and protected by an automatic reset thermal overload switch. Motor(s) to have double extended shaft and direct drive, double inlet, dynamically balanced forward curved squirrel cage blower wheels.

**ELECTRICAL WIRING**  
 Each motor to have a watertight junction box to be mounted on bottom center of each motor/fan assembly. Specify for alternate locations.

**GUARANTEE**  
 Shall be five years on all parts.

An equipment specification can be prepared by combining the standard features with the checked boxes below indicating the selection of the optional features.

**OPTIONAL FEATURES**  
 When checked below, the air curtain will be supplied with the following special features.

- Explosion proof motors
- Two speed motor (Available in single phase only)
- Door microswitch(s) (20 amp) for automatic on/off control. Turns air curtain on when door is opened and off when door is closed. Field installed.
  - Plunger type
  - Roller type

Note: Mars® recommends the use of a motor control panel on 3 phase motors whenever a door microswitch is used to start and stop the air curtain. One door microswitch can directly control one 1 HP, one or two 1/2 HP or one or two 1/3 HP single phase motors without the need for a motor control panel.

- Wall mounted control panel
- Factory mounted control panel on air curtain

Indicate the total number of motors to be powered through panel

1     2     3     4     5     6

- Plates for side extension of mounting points
  - 5 inch extension
  - 7 inch extension
  - 9 inch extension
- Adjustable mounting brackets to clear any wall obstruction of air flow
  - 2 ? inch clearance
  - 4 inch clearance
  - 7 inch clearance
  - 10 inch clearance
- Extended Wall Mounting Brackets for drum type roll-up doors
  - 10 inch clearance
  - 16 inch clearance
  - 19 inch clearance
  - 23 inch clearance
- All stainless steel housing
- Washable aluminum air filter
  - In lieu of adjustable inlet air louver
  - In conjunction with adjustable inlet air louver