




# CONCRETE/ASPHALT BASE

P.O. BOX 239, 4393 DISCOVERY LINE  
 PETROLIA, ONTARIO  
 N0N 1R0  
 PHONE: (800) 263-2363  
 PHONE: (519) 882-8799  
 FAX: (519) 882-2697  
 EMAIL: alltinfo@sosurfaces.com



## LEGEND:

- ① SofCRETE (See Specifications for Depth and Color). 1.0% Slope - 1/4" / 12" (6mm / 300mm). 1/4" Diameter Continuous Bead of SoftILE Adhesive at Each KrosLOCK Joint.
- ② 6 X 6" (150 X 150mm) PT Timber Edge Supported by Pst at 8' (2.45m) On Center (Or Approved Alternative).
- ③ Sod and Topsoil
- ④ Compacted Granular A (Type I) To 95% S.P.D. (See Specifications for Depth).
- ⑤ Compacted Subgrade.
- ⑥ Concrete or Asphalt Base (See Specifications for Depth and Details).

## NOTES:

- 1. Test planarity using a water flood coat. Repair area of standing water in excess of thickness of a nickel 1/4" (6mm).
- 2. Install 2" (50mm) diameter weeping holes at 3' (900mm) on center at curb when area drains in that direction.
- 3. Allow the following cure times:
  - Asphalt/Concrete base - 28 Days.
- 4. On asphalt surfaces with a solid adhesive coat:
  - Do not use diesel fuel to lubricate paving equipment. Use soapy water.
  - Do not refuel paving equipment on asphalt surface area to be covered with adhesive.

THICKNESS	DROP HEIGHT (FT)		REVISIONS						
	WITH 5YR PERFORMANCE WARRANTY	WITH 5YR PERFORMANCE WARRANTY	REV	DESCRIPTION	DATE	APPR			
	BASIC & PLUS	PREMIUM (EPDM)							
1.50"	3.0	3.0	0	ORIGINAL ISSUE REVISED	03/13/03 10/10/07				
2.00"	4.0	4.0	1						
2.50"	5.0	5.0							
3.00"	6.0	6.0							
3.50"	7.0	7.0							
4.00"	8.0	8.0							
4.50"	9.0	9.0							
5.00"	10.0	10.0							
			SIZE A				FSCM NO.	DWG NO. 2000-001	REV 0
FILE NAME	A0001SK12	PREPARED BY	GOSS. B				SCALE	NTS	SHEET SK12