




DETAIL 'B' CONCRETE/ASPHALT BASE

P.O. BOX 239, 4393 DISCOVERY LINE
 PETROLIA, ONTARIO
 N0N 1R0
 PHONE: (800) 263-2363
 PHONE: (519) 882-8799
 FAX: (519) 882-2697
 EMAIL: alltinfo@sofsurfaces.com



LEGEND:

- ① SofTILE® (See Specifications for Depth and Color).
- ② 1/2" Diameter Continuous Bead of SofTILE Adhesive at Each KrosLOCK Joint.
- ③ 1" / 12" (25mm / 300mm) Sloped SofRAMP® (ADA) or Standard SofRAMP® Jr (See Specifications for Details).
- ④ Apply SofTILE Adhesive to Entire Bottom Edge and locking joint of SofRAMP.
- ⑤ Cut off "Lock" at any Retainer. Use Adhesive on the Retainer, and Under First 12" (300mm) of Perimeter Tiles.
- ⑥ Concrete or Asphalt Base and Curb (See Specifications for Depth and Details).
- ⑦ Compacted Granular A Type I
- ⑧ Compacted Subgrade.
- ⑨ Minimum 1.0% Slope - 1/4" / 12" (6mm / 300mm).

NOTES:

1. Test surface grade using a water flood coat. Repair areas of standing water in excess of thickness of 1/4" (6mm).
2. Install 3/4" (50mm) weeping holes every 3' at lowest point of slope.
3. Allow the following cure times:
 - Asphalt/Concrete base - 21 Days/28 Days.
4. On asphalt surfaces with a solid adhesive coat:
 - Do not use diesel fuel to lubricate paving equipment. Use soapy water.
 - Do not refuel paving equipment on asphalt surface area to be covered with adhesive.

| THICKNESS | CRITICAL FALL HEIGHT (FT) | | REVISIONS | | | | |
|-----------|---|---|-----------|-------------|---------------------|----------|------|
| | WITH 10 YEAR PERFORMANCE WARRANTY PLUS SERIES | WITH 10 YEAR PERFORMANCE WARRANTY PREMIUM SERIES (EPDM) | REV | DESCRIPTION | DATE | APPR | |
| | 1.75" | 3.0 | 3.0 | 0 | ORIGINAL ISSUE | 8/30/04 | |
| 2.00" | 4.0 | 4.0 | 1 | UPDATED | 10/21/04 | | |
| 2.25" | 5.0 | 5.0 | 2 | UPDATED | 8/30/05 | | |
| 2.50" | 6.0 | 6.0 | 3 | UPDATED | 02/02/06 | | |
| 2.75" | 7.0 | 7.0 | | | | | |
| 3.75" | 8.0 | 8.0 | | | | | |
| 4.00" | 10.0 | 10.0 | | | | | |
| | | | SIZE A | FSCM NO. | DWG NO. 2000-001 | REV 3 | |
| FILE NAME | A0001SK12 | PREPARED BY | B.GOSS | SCALE | NTS | SHEET | SK12 |