



EXPANDABLE STRETCHER FRAME WITH EXTENDER PIPES FOR GW30V60803 TO GW30V60806 SECTIONS



TYPICAL WOOD STRETCHER FRAME FOR GW30V60803 SECTION SIZE



TEMPORARY STRETCHING METHOD FOR INSTALLATION OF GW30V GEOWEB SECTIONS

TABLE		
EXPANDED GEOWEB SECTION LENGTH		
CELLS LONG	SECTION LENGTH (mm)	SECTION LENGTH (in)
3	800	31.5
4	1067	42
5	1334	52.5
6	1600	63
7	1867	73.5

- PARTS LIST - EXPANDABLE STRETCHER FRAME**
- 16 13 mm (1/2") X 190 mm (7 1/2") THREADED ROD
 - 32 13 mm (1/2") NUTS WITH WASHERS
 - 4 13 mm (1/2") X 90 mm (3 1/2") BOLTS
 - 4 13 mm (1/2") NUTS WITH WASHERS
 - 4 50.8 mm (2") ID ELBOWS
 - 4 49.2 mm (1 15/16") OD PIPE
 - 2 50.8 mm (2") ID EXTENDER PIPE

- PIPE AND ELBOW DIMENSIONS ARE BASED ON STANDARD STEEL PIPE SIZES. DIMENSIONS MAY VARY SLIGHTLY FOR STRETCHER FRAMES FABRICATED WITH ALUMINUM OR PVC PIPE AND ELBOW COMPONENTS.
- EXTENDER PIPE DIMENSIONS**
- 3 TO 4 CELL LONG GW30V GEOWEB SECTIONS - 561 mm (22.1")
 - 5 TO 6 CELL LONG GW30V GEOWEB SECTIONS - 1095 mm (43.1")
 - 7 CELL LONG GW30V GEOWEB SECTIONS - 1361 mm (53.6")

- EXTENDER PIPE DIMENSIONS MAY VARY DEPENDING UPON ELBOW DIMENSIONS. CHECK ELBOW DIMENSIONS BEFORE DRILLING HOLES IN PIPE AND EXTENDER PIPE.

- PARTS LIST - WOOD STRETCHER FRAME FOR GW30V60803 SECTIONS**
- 16 13 mm (1/2") X 203 mm (8") THREADED ROD
 - 8 375 mm (3/8") X 102 mm (4") CARRIAGE BOLTS
 - 48 375 mm (3/8") FLAT WASHERS
 - 48 375 mm (3/8") HEX NUTS
 - 3 2" X 4" X 8.66" LUMBER

- PARTS LIST - TEMPORARY STRETCHER BARS**
- 8 12.7 mm (1/2") X 1105 mm (43.5") STEEL BARS PER GEOWEB SECTION



PRESTO GEOSYSTEMS®

THE GEOWEB® EARTH RETENTION SYSTEM INSTALLATION TOOLS

GEOSYSTEMS®, GEOWEB®, AND ATRA® ARE REGISTERED TRADEMARKS OF PRESTO PRODUCTS COMPANY.

DATE	APRIL, 2008	FILE NAME	GWRWF.DWG
SCALE	NTS	SHEET	6