




DETAIL 'A' GRANULAR BASE

P.O. BOX 239, 4393 DISCOVERY LINE
 PETROLIA, ONTARIO
 N0N 1R0
 PHONE: (800) 263-2363
 PHONE: (519) 882-8799
 FAX: (519) 882-2697
 EMAIL: alltinfo@sosurfaces.com



LEGEND:

- ① SofTILE® (See Specifications for Depth and Color).
- ② 1/2" (12mm) Diameter Continuous Bead SofTILE® Adhesive at Each KrosLOCK Joint.
Cut off "Lock" at any Retainer. Use SofTILE® Adhesive on First 12" (300mm) of the Bottom Edge of Perimeter Tile.
- ③ Minimum 1.0% Slope - 1/4" / 12" (6mm / 300mm) of Sub Base.
- ④ Geotextile Terrafix 200R (or Equivalent) Overlap by 12" (300mm) and Tape Joints.
- ⑤ Minimum 1/2" (12mm) Fine Crushed Granite Screenings (As Required) to achieve a Max 1/4" (6mm) Variation in Grade When Measured With a 10' (3m) Straight Edge in any Direction.
- ⑥ Compacted Granular A (Type I) (0-3/4") To 95% S.P.D. (See Specifications for Depth).
- ⑦ 4" (100mm) Perforated Plastic or PVC Drain Tile at 16' (4.9m) On Center.
- ⑧ 3/4" (20mm) Clear Stone.
- ⑨ Wrap with Geotextile Terrafix 200R.
- ⑩ Compacted Subgrade.

NOTES:

1. Ensure subsoil drains towards perforated drain tile.
2. Install perforated drain tile at 16' (4.8m) on center as well as around the perimeter of the SofTILE® installation. Drain to nearest storm collection system.
3. Back fill around perforated drain tile with 3/4" (20mm) clear stone to 6" (150mm) radius around drain tile. Wrap with Geotextile Terrafix 200R to prevent the compacted aggregate from obstructing the drain.

THICKNESS	CRITICAL FALL HEIGHT (FT)		REVISIONS				
	WITH 10 YEAR PERFORMANCE WARRANTY	WITH 10 YEAR PERFORMANCE WARRANTY	REV	DESCRIPTION	DATE	APPR	
	PLUS SERIES	PREMIUM SERIES (EPDM)					
1.75"	3.0	3.0	0	EDITED ISSUE UPDATED UPDATED UPDATED	08/24/04 10/21/04 02/02/06 01/09/07		
2.00"	4.0	4.0	1				
2.25"	5.0	5.0	2				
2.50"	6.0	6.0	3				
2.75"	7.0	7.0	SIZE A	FSCM NO.	DWG NO. 2000-001	REV 2	
3.75"	8.0	8.0					
4.00"	10.0	10.0					
FILE NAME	A0001SK11	PREPARED BY	B. GOSS	SCALE	NTS	SHEET	SK11