

MAX HEIGHT ABOVE AVERAGE  
LEVEL OF ADJOINING GROUND  
ADJACENT TO BUILDING

PANEL SCREWS PER MFG'S  
RECOMMENDATIONS FOR #  
AND LOCATIONS

16 GA. 4" Z SECTION OR  
16 GA. 1 1/2" HAT SECTION

TYPICAL FIELD CONNECTOR

TYPICAL FLATTEN TRIM AND PIERCE,  
OPTIONAL END CONNECTOR

PANELING

Ø2.5" TUBING 11GA., OR 16GA. (TYP)

5/16" SS BOLT WITH SEALING  
WASHER (8) TOTAL PER BASE CAP

SPROCKET LOCK  
CONNECTOR

T/3 TEK SCREWS TYP

TYPICAL "BASE CONNECTOR"

TYPICAL "BASE CAP"

TYPICAL "BASE SUPPORT"

METHOD AND HARDWARE FOR  
ATTACHMENT TO STRUCTURE  
DET. BU STRUCT. CALC'S.

DISTANCE BETWEEN BASE SUPPORTS  
DETERMINED BY STRUCT. CALC'S

# TYPICAL ROOFSCREEN TWO MEMBER FRAME

<small>UNLESS OTHERWISE SPECIFIED ALL DIM'S ARE IN INCHES AND INCLUDE APPLIED FINISH TOLERANCES</small> <small>1/16" 3/32" 1/8" 3/16" 1/4" 5/16" 3/8" 1/2" 5/8" 3/4" 1" 1 1/4" 1 1/2" 2" 2 1/2" 3" 3 1/2" 4" 4 1/2" 5" 5 1/2" 6" 6 1/2" 7" 7 1/2" 8" 8 1/2" 9" 9 1/2" 10"</small>	347 Coral Street Santa Cruz, CA		
	TITLE: TWO MEMBER FRAME ASSEMBLY 95060		
	MATL: N/A	DWG NO:	REV A
	FINISH: N/A	FRAME_TM	SHEET 1 OF 1
HARDNESS: --	SCALE: 0.125	DRAWN BY: MDH	