




# CONTAINED SOFTILE OVER AGGREGATE

P.O. BOX 239, 4393 DISCOVERY LINE  
 PETROLIA, ONTARIO  
 N0N 1R0  
 PHONE: (800) 263-2363  
 PHONE: (519) 882-8799  
 FAX: (519) 882-2697  
 EMAIL: allinfo@sosurfaces.com



## LEGEND:

- ① SofTILE® (See Specifications for Depth and Color).
- ② 1/2" Diameter Continuous Bead of SofTILE® Adhesive at Each KrosLOCK Joint.
- ③ Minimum 1.0% Slope - 1/4" / 12" (6mm / 300mm).
- ④ Containing Sidewalk
- ⑤ Underlying Concrete Lip (6")
- ⑥ Geotextile Terrafix 200R (or Equivalent) Overlap by 12" (300mm) and Tape Joints.
- ⑦ Minimum 1/2" (12mm) Fine Crushed Granite Screenings (As Required) to Achieve a Max 1/4" (6mm) Variation in Grade When Measured With a 10' (3m) Straight Edge in any Direction.
- ⑧ Compacted Granular A (Type I) (3/4" minus) To 95% S.P.D. (See Specifications for Depth).
- ⑨ 3/4" (20mm) Clear Stone, 6" Radius.
- ⑩ 4" (100mm) Perforated Plastic or PVC Drain Tile at 16' (4.9m) On Center.
- ⑪ Compacted Subgrade.

## NOTES:

1. Ensure subsoil drains towards perforated drain tile.
2. Install perforated drain tile at 16' (4.8m) on center as well as around the perimeter of the SofTILE® installation. Drain to nearest storm collection system. Surround Clear Stone with Geotextile Terrafix 200R to Prevent Obstruction.
3. Back fill around perforated drain tile with 3/4" (20mm) clear stone to 6" (150mm) radius around tile.

THICKNESS	CRITICAL FALL HEIGHT (FT)		REVISIONS			
	WITH 10 YEAR PERFORMANCE WARRANTY	WITH 10 YEAR PERFORMANCE WARRANTY	REV	DESCRIPTION	DATE	APPR
	PLUS SERIES	PREMIUM SERIES (EPDM)				
1.75"	3.0	3.0	0	ORIGINAL ISSUE	8/31/04	
2.00"	4.0	4.0	1	UPDATED	11/28/05	
2.25"	5.0	5.0	2	UPDATED	02/02/06	
2.50"	6.0	6.0	3	UPDATED	3/13/07	
2.75"	7.0	7.0				
3.75"	8.0	8.0	SIZE	FSCM NO.	DWG NO.	REV
4.0"	10.0	10.0	A		2000-001	3
FILE NAME	PREPARED BY	SCALE	SHEET			
Contained SofTILE	B. GOSS		SK17			