




DETAIL 'D' CONCRETE EDGE

P.O. BOX 239, 4393 DISCOVERY LINE
 PETROLIA, ONTARIO
 N0N 1R0
 PHONE: (800) 263-2363
 PHONE: (519) 882-8799
 FAX: (519) 882-2697
 EMAIL: alltinfo@sofsurfaces.com



LEGEND:

- ① SofTILE® (See Specifications for Depth and Color).
- ② 1/2" Diameter Continuous Bead of SofTILE Adhesive at Each KrosLOCK Joint. Apply Adhesive to Concrete and SofTILE Edge.
- ③ Minimum 1.0% Slope - 1/4" / 12" (6mm / 300mm).
- ④ Concrete Retainer Lip. Concrete Depth and Strength to Specifications.
- ⑤ Minimum 1/2" (12mm) Fine Crushed Granite Screenings (As Required) to achieve a Max 1/4" (6mm) Variation in Grade. When Measured With a 10' (3m) Straight Edge in any Direction.
- ⑥ Compacted Granular A (Type I) To 95% S.P.D. (See Specifications for Depth).
- ⑦ 4" (100mm) Perforated Plastic or PVC Drain Tile at 16' (4.9m) On Center. Wrap with Geotextile Terrafix 200R.
- ⑧ 3/4" (20mm) Clear Stone.
- ⑨ Compacted Subgrade.
- ⑩ Geotextile Terrafix 200R (or Equivalent) Overlap by 12" (300mm) and Tape Joints.

NOTES:

1. Ensure subsoil drains towards perforated drain tile.
2. Install perforated drain tile at 16' (4.8m) on center as well as around the perimeter of the SofTILE® installation. Drain to nearest storm collection system.
3. Back fill around perforated drain tile with 3/4" (20mm) clear stone to 6" (150mm) radius around drain tile.
4. Wrap with Geotextile Terrafix 200R to prevent clogging.

THICKNESS	CRITICAL FALL HEIGHT (FT)		REVISIONS			
	WITH 10 YEAR PERFORMANCE WARRANTY	WITH 10 YEAR PERFORMANCE WARRANTY	REV	DESCRIPTION	DATE	APPR
	PLUS SERIES	PREMIUM SERIES (EPDM)	0	ORIGINAL ISSUE	8/31/04	
1.75"	3.0	3.0	1	UPDATED	10/21/04	
2.00"	4.0	4.0	2	UPDATED	02/02/06	
2.25"	5.0	5.0				
2.50"	6.0	6.0				
2.75"	7.0	7.0				
3.75"	8.0	8.0				
4.00"	10.0	10.0				
			SIZE	FSCM NO.	DWG NO.	REV
			A		2000-001	2
FILE NAME		PREPARED BY	SCALE	NTS	SHEET	
A0001SK14		B.GOSS			SK14	