



SECTION

1. CONTINUOUS STRUCTURAL ANGLE
2. ISOWALL BRAND INSULATING PANEL
3. 1 1/2" X 3 1/2" X 24" MIN. TREATED WOOD SPLINE
4. 2" X THICKNESS X 2" X 16 GA. GALV. STEEL CHANNEL SEALED WITH BUTYL CAULK AND FASTENED TO BOTH PANEL FACINGS WITH #10 PAN HEAD TEK SCREWS SPACED 8" O.C.
5. 5/16" X 3 1/2" CORROSION RESISTANT LAG SCREW-2 PER SPLINE
6. #14 X LENGTH CORROSION RESISTANT SCREW-2 PER SPLINE
7. ROOF INSULATION
8. SINGLE PLY ROOF MEMBRANE SEALED AND FASTENED TO EXTERIOR PANEL FACING IN ACCORDANCE WITH MEMBRANE MANUFACTURER'S INSTRUCTIONS
9. FOAMED-IN-PLACE URETHANE
10. GRAVEL STOP AND FACIA