




DETAIL 'A'
SofTILE Contained By SofRAMP

P.O. BOX 239, 4393 DISCOVERY LINE
PETROLIA, ONTARIO
N0N 1R0
PHONE: (800) 263-2363
PHONE: (519) 882-8799
FAX: (519) 882-2697
EMAIL: alltinfo@sofsurfaces.com



LEGEND:

- ① SofTILE® (See Specifications for Depth and Color).
- ② 1/2" Diameter Continuous Bead of SofTILE Adhesive at Each KrosLOCK Joint.
- ③ 1" / 12" (25mm / 300mm) Sloped SofRAMP® (ADA) or Standard SofRAMP® Jr (See Specifications for Details).
- ④ Apply SofTILE Adhesive to Entire Bottom Edge and locking joint of SofRAMP.
- ⑤ Cut off "Lock" at any Retainer. Use Adhesive on the Retainer, and Under First 12" (300mm) of Perimeter Tiles.
- ⑥ Concrete or Asphalt Base and Curb (See Specifications for Depth and Details).
- ⑦ Compacted Granular A Type I
- ⑧ Compacted Subgrade.
- ⑨ Minimum 1.0% Slope - 1/4" / 12" (6mm / 300mm).

THICKNESS	CRITICAL FALL HEIGHT (FT)		REVISIONS				
	WITH 10 YEAR PERFORMANCE WARRANTY	WITH 10 YEAR PERFORMANCE WARRANTY	REV	DESCRIPTION	DATE	APPR	
	PLUS SERIES	PREMIUM SERIES (EPDM)					
1.75"	3.0	3.0	0	ORIGINAL ISSUE	02/02/06		
2.00"	4.0	4.0					
2.25"	5.0	5.0					
2.50"	6.0	6.0					
2.75"	7.0	7.0					
3.75"	8.0	8.0					
4.00"	10.0	10.0					
							SIZE
			A		2000-001	0	
File Name	A0001SK1	Prepared By	B.GOSS	SCALE	NTS	SHEET	SK1