




DETAIL 'G' BURIED CURB RETAINER

P.O. BOX 239, 4393 DISCOVERY LINE
 PETROLIA, ONTARIO
 N0N 1R0
 PHONE: (800) 263-2363
 PHONE: (519) 882-8799
 FAX: (519) 882-2697
 EMAIL: alltinfo@sofsurfaces.com



LEGEND:

- ① SofTILE® (See Specifications for Depth and Color).
- ② 1/2" Diameter Continuous Bead of SofTILE® Adhesive at Each KrosLOCK Joint.
- ③ Minimum 1.0% Slope - 1/4" / 12" (6mm / 300mm).
- ④ Sod and Topsoil.
- ⑤ Geotextile Terrafix 200R (or Equivalent) Overlap by 12" (300mm) and Tape Joints.
- ⑥ Standard 6 1/2" (165mm) X 5 1/4" (133mm) X 6' (1.8m) Parking Curb - Inverted or Wood Timber.
- ⑦ Minimum 1/2" (12mm) Fine Crushed Granite Screenings (As Required) to Achieve a Max 1/4" (6mm) Variation in Grade When Measured With a 10' (3m) Straight Edge in any Direction.
- ⑧ 3/4" (20mm) Clear Stone, 6" Radius.
- ⑨ Compacted Granular A (Type I) To 95% S.P.D. (See Specifications for Depth).
- ⑩ 4" (100mm) Perforated Plastic or PVC Drain Tile at 16' (4.9m) On Center.
- ⑪ Compacted Subgrade.

NOTES:

1. Ensure subsoil drains towards perforated drain tile.
2. Install perforated drain tile at 16' (4.8m) on center as well as around the perimeter of the SofTILE® installation. Drain to nearest storm collection system. Wrap Perforated Drain with Geotextile Terrafix 200 R to Prevent Obstruction.
3. Back fill around perforated drain tile with 3/4" (20mm) clear stone to 6" (150mm) radius around tile.

THICKNESS	CRITICAL FALL HEIGHT (FT)		REVISIONS			
	WITH 10 YEAR PERFORMANCE WARRANTY	WITH 10 YEAR PERFORMANCE WARRANTY	REV	DESCRIPTION	DATE	APPR
	PLUS SERIES	PREMIUM SERIES (EPDM)				
1.75"	3.0	3.0	0	ORIGINAL ISSUE UPDATED UPDATED	8/31/04 11/28/05 02/02/06	
2.00"	4.0	4.0	1			
2.25"	5.0	5.0	2			
2.50"	6.0	6.0				
2.75"	7.0	7.0				
3.75"	8.0	8.0	SIZE	FSCM NO.	DWG NO.	REV
4.00"	10.0	10.0	A		2000-001	2
FILE NAME	PREPARED BY		SCALE	SHEET		
Buried Curb	B. GOSS			SK17		