




LEGEND







TOP MOUNT POST

Œ CENTERLINE

F.F. FINISHED FLOOR

TYP TYPICAL CONDITION; APPLIES ELSEWHERE AT SIMILAR LOCATIONS

NOTES:

TOP RAIL NOT SHOWN FOR CLARITY.

*OLYMPUS TM36W AGS SPECIFICATION DRAWING TOP MOUNT - WOOD TOP


 \mathcal{C}


7873 NE DAY ROAD BAINBRIDGE ISLAND, WA 98110

OLYMPUS

36"







TYPICAL END POST **ELEVATION** SCALE: NONE

TYPICAL INTERMEDIATE POST ELEVATION SCALE: NONE



NOTES:

- 1. TOP RAIL SHOULD BE SELECTED SO THAT ALL GOVERNING CODE REQUIREMENTS ARE SATISFIED. THESE INCLUDE SHAPE, STRENGTH AND RAILING HEIGHT.
- DECK STRUCTURE CAN VARY GREATLY. IT IS THE RESPONSIBILITY OF THE CUSTOMER TO VERIFY THAT THE SUPPORTING STRUCTURE IS ADEQUATE TO MEET THE LOAD REQUIREMENTS OF THE GOVERNING BUILDING CODE(S). AGS Stainless Inc. RECOMMENDS CONSULTING A DESIGN OR CONSTRUCTION PROFESSIONAL TO ADDRESS THESE ISSUES.

 \mathcal{C} \sim

*OLYMPUS TM36W AGS

SPECIFICATION DRAWING

- WOOD **TOP MOUNT** OLYMPUS







SPECIFICATION DRAWING TOP MOUNT - WOOD TOP

OLYMPUS









OUTSIDE CORNER POST LAYOUT - 90°

INSIDE CORNER POST LAYOUT - 90° В SCALE: NONE





OUTSIDE CORNER POST LAYOUT - 45°

INSIDE CORNER POST LAYOUT - 45° D



NOTE:

THE LAYOUTS SHOWN MAY VARY AS THE ANGLE CHANGES. MAKE SURE YOU CHOOSE A POST LAYOUT SO THAT TWO CLOSEST POINTS OF THE ADJACENT POSTS IS LESS THAN 4".