


Approval

Confirmation

Making

■ PRODUCT DRAWING



■ SPECIFICATIONS

Power source	Power-over-Ethernet (IEEE 802.3af Class 0)
Current consumption	Standby 33mA, maximum 70mA
Type of communication	Hands-free: Automatic voice switching
LAN	Ethernet (10BASE-T, 100BASE-TX) Auto MDI/MDI-X-compatible
Audio codec	G. 711 (μ -law, A-law), G. 722
Protocol	IPv4, IPv6, TCP, UDP, SIP, HTTP, HTTPS, RTSP, RTP, RTCP, IGMP, MLD, SMTP, SFTP, DHCP, NTP, DNS
Encryption method	TLS1.0, TLS1.1, TLS1.2
Packet delivery	Unicast
Number of called stations	20 stations
Ambient temperature	-40~+60°C (-40~+140° F)
Mounting	Flush wall-mount
Electrical box	2-gang box (Depth: 52.5mm (2-1/16") or more)
Material	Front panel: Stainless steel, vertical alignment finished Main unit: Self-extinguishing ABS resin
Unit color	Front panel: silver/ Main unit: black
Weight	390g (approx.) (0.86 lbs)
IP rating	IP65
IK rating	IK08

DESCRIPTION	FIG. NAME	UNIT	DATE
AUDIO ONLY DOOR STATION	PRODUCT DRAWING/SPECIFICATIONS	mm	
MODEL NO.	FIG. NO.	PAGE	REVISION
		1/5	1

AIPHONE