


Approval

Confirmation

Making

PRODUCT DRAWING



SPECIFICATIONS

Power source	Power-over-Ethernet (IEEE 802.3af/at Class 0) / 24V DC External power supply		
Current consumption	Power-over-Ethernet Standby: 55mA / Standby with continuous recording: 77mA Maximum: 155mA 24V DC External power supply Standby: 94mA / Standby with continuous recording: 140mA Maximum: 300mA		
Type of communication	Hands-free: automatic voice switching		
Camera	1/3-type color CMOS SXVGA 1280 x 960 (approx. 1.2 million pixels)		
Minimum illumination	5 lux		
LAN	Ethernet (10BASE-T, 100BASE-TX), Auto MDI/MDI-X-compatible		
Audio codec	G.711 (μ -law, A-law), G.722		
Video codec	H.264/AVC, Motion JPEG		
Protocol	IPv4, IPv6, TCP, UDP, SIP, HTTP, HTTPS, RTSP, RTP, RTCP, IGMP, MLD, SMTP, SFTP, DHCP, NTP, DNS		
Encryption method	TLS1.0, TLS1.1, TLS1.2		
Packet delivery	Unicast, Multicast		
Number of called stations	20 stations		
Ambient temperature	-40~+60°C (-40~+140° F)		
Mounting	Flush wall-mount		
Material	Front panel: stainless steel, vertical alignment finished / Main unit: self-extinguishing ABS resin / Box: SPCC 1.2		
Unit color	Front panel: silver / Main unit: black / Box: black (Electrodeposition Coating)		
Weight	Unit: approx. 1.5kg (3.3 lbs) / Box: approx. 860g (1.9 lbs)		
IP rating	IP65		
IK rating	IK08		
Remarks	ONVIF Profile S support		
DESCRIPTION	FIG. NAME	UNIT	DATE
VIDEO DOOR STATION	PRODUCT DRAWING/SPECIFICATIONS	mm	
MODEL NO.	FIG. NO.	PAGE	REVISION
		1/5	1
AIPHONE			