


5" FLUTED LINEAL



- A. 5.000 ± 0.025
- B. 1.310 ± 0.015
- C. 0.360 ± 0.010
- D. 0.900 ± 0.010
- E. 0.675 ± 0.015
- F. 0.665 ± 0.030
- G. 0.760 ± 0.015
- H. 0.625 ± 0.015
- J. 1.385 ± 0.030
- K. 0.925 ± 0.030
- L. 2.175 ± 0.030
- M. 0.120 ± 0.10

WALL THICKNESS EXPOSED = $.044 \pm .002$
 WEIGHT PER FOOT - - - = .295 LBS.
 OVERALL LENGTH - - - = $20' \pm 1/4''$
 WEEP HOLE - - - - - = N/A
 WARP - - - - - = 1"
 NAIL CENTER - - - - - = N/A

