


Approval

Confirmation

Making

## ■ PRODUCT DRAWING



## ■ SPECIFICATIONS

Power source	Power-over-Ethernet (IEEE 802.3af Class 0)
Current consumption	Standby 66mA, maximum 155mA
Type of communication	Hands-free: Automatic voice switching/touch-to-talk
Monitor	7" TFT LCD display, WVGA 800 x 480 (approx. 1.15 million pixels)
Camera	1/4-type CMOS, VGA 640 x 480 (approx. 300,000 pixels)
LAN	Ethernet (10BASE-T, 100BASE-TX) Auto MDI/MDI-X-compatible
Audio codec	G.711 ( $\mu$ -law, A-law), G.722
Video codec	H.264/AVC, Motion JPEG
Protocol	IPv4, IPv6, TCP, UDP, SIP, HTTP, HTTPS, RTSP, RTP, RTCP, IGMP, MLD, SMTP, SFTP, DHCP, NTP, DNS
Encryption method	TLS1.0, TLS1.1, TLS1.2
Packet delivery	Unicast, Multicast
Number of stations in address book	500 stations
Ambient temperature	0~40°C (32~104° F)
Mounting	Desktop use (with desktop stand) or wall-mount
Electrical box	3-gang box
Material	Self-extinguishing ABS resin
Unit color	flat black (N2 Munsell Approximation)
Weight	680g (approx.) (1.5 lbs) (when used with desk stand: 870g (approx.) (1.92 lbs))
Remarks	ONVIF Profile S support

DESCRIPTION	FIG. NAME	UNIT	DATE
<b>MASTER STATION</b>	PRODUCT DRAWING/SPECIFICATIONS	mm	
MODEL NO.	FIG. NO.	REVISION	<b>AIPHONE</b>
	PAGE	1	
	1/8		