


# 3/4" X 7.00" FLUTED OUTSIDE CORNER POST



- A. TOTAL PANEL WIDTH =  $7.00 \pm 0.050$
- B. PANEL WIDTH =  $1.250 \pm 0.010$
- C. PANEL GAP =  $0.800 \pm 0.010$
- D. BEAD WIDTH =  $0.380 \pm 0.010$
- E. SIDING POCKET WIDTH =  $0.750 \pm 0.040$
- F. RADIUS  $0.150 \pm 0.015$
- G. EXPOSED BEAD WIDTH =  $0.300 \pm .040$
- H. SIDING POCKET WIDTH =  $0.750 \pm 0.040$
- J. SIDING POCKET DEPTH =  $2.250 \pm 0.040$

WALL THICKNESS EXPOSED =  $.048 \pm .002$   
 WEIGHT PER FOOT - - - = .300 LBS.  
 OVERALL LENGTH - - - =  $10' \pm 1/4''$   
 WARP - - - - - =  $1/2''/\text{PANEL}$   
 WEEP HOLE - - - - - = N/A  
 NAIL CENTER - - - - - = N/A

