



SECTION A-A
SUPPORT HANGER DETAIL

HEADROOM REQUIREMENTS		
DRUM	HIGH LIFT	MINIMUM HEADROOM
D400-54	9" - 54"	HIGH LIFT + 10"
D525-54	9" - 54"	HIGH LIFT + 11"
D575-120	9" - 120"	HIGH LIFT + 13-1/2"
D6375-164	9" - 164"	HIGH LIFT + 14-1/4"

* ADD 4" FOR OPERATOR.

FLOOR TO SHAFT CENTER REQUIREMENTS		
DRUM	HIGH LIFT	MINIMUM HEADROOM
D400-54	9" - 54"	DH + HL + 6-1/2"
D525-54	9" - 54"	DH + HL + 6-7/8"
D575-120	9" - 120"	DH + HL + 8-1/4"
D6375-164	9" - 164"	DH + HL + 8-1/4"

DH = DOOR HEIGHT
HL = HIGH LIFT

NOTE: CONTACT ENGINEERING DEPARTMENT FOR PITCH CUT DETAIL.

HIGH LIFT TAPERED REVERSE ANGLE MOUNT TRACK SET DETAIL