



SECTION A-A
SUPPORT HANGER DETAIL

| HEADROOM REQUIREMENTS | | |
|-----------------------|-----------|---------------------|
| DRUM | HIGH LIFT | MINIMUM HEADROOM |
| D400-54 | 9" - 54" | HIGH LIFT + 9" |
| D525-54 | 9" - 54" | HIGH LIFT + 10" |
| D575-120 | 9" - 120" | HIGH LIFT + 12-1/2" |
| D6375-164 | 9" - 164" | HIGH LIFT + 13-1/2" |

* ADD 4" FOR OPERATOR.

| FLOOR TO SHAFT CENTER REQUIREMENTS | | |
|------------------------------------|-----------|-----------------------|
| DRUM | HIGH LIFT | FLOOR TO SHAFT CENTER |
| D400-54 | 9" - 54" | DH + HL + 5-9/16" |
| D525-54 | 9" - 54" | DH + HL + 5-15/16" |
| D575-120 | 9" - 120" | DH + HL + 7-5/16" |
| D6375-164 | 9" - 164" | DH + HL + 7-5/16" |

DH = DOOR HEIGHT
HL = HIGH LIFT
NOTE: CONTACT ENGINEERING DEPARTMENT FOR PITCH CUT DETAIL.

HIGH LIFT BRACKET MOUNT TRACK SET DETAIL