

Model E-V-G-PVCCM

Glass Venting Curb Mount Skylight (slope roof detail)

Artistic Skylights conform to and exceed test requirements of the following criteria:
 CAN/CGSB 63.14-M89 (1989) (Plastic Skylights): AAMA / WDMA / CSA 101 / IS.2 / A440
 (2008) (NAFS North American Fenestration Standard / Specification for Windows, Doors and
 Skylights): CSA A440.2 (2009) (Fenestration Energy Performance)

Skylights are suitable for use on all types of slope roofs. Designed for mounting on 1½" (38mm) curbs with flashing (by others), these units provide excellent performance in all geographic locations.

- Flashing kits available for asphalt shingle roofs
- Custom sizes are available upon request
- Custom applications available

Model E-V-G-PVCCM Available Sizes

Model #	B x B Dimensions	Glass Glazing Type	Flashing Kit QTY	QTY
EV-G-PVCCM 2828	22¼" x 22¼" (565mm x 565mm)			
EV-G-PVCCM 2836	22¼" x 30¼" (565mm x 768mm)			
EV-G-PVCCM 2852	22¼" x 46¼" (565mm x 1175mm)			
EV-G-PVCCM 2860	22¼" x 55" (565mm x 1397mm)			
EV-G-PVCCM 2876	22¼" x 69½" (565mm x 1765mm)			
EV-G-PVCCM 3636	30¼" x 30¼" (768mm x 768mm)			
EV-G-PVCCM 3642	30¼" x 37" (768mm x 940mm)			
EV-G-PVCCM 3652	30¼" x 46¼" (768mm x 1175mm)			
EV-G-PVCCM 3660	30¼" x 55" (768mm x 1397mm)			
EV-G-PVCCM 4242	37" x 37" (940mm x 940mm)			
EV-G-PVCCM 4252	37" x 46¼" (940mm x 1175mm)			
EV-G-PVCCM 5252	46¼" x 46¼" (1175mm x 1175mm)			
EV-G-PVCCM CUST.				
EV-G-PVCCM CUST.				

Glass Glazing Available

Glass Glazing	Colour Code	Glass Glazing	Colour Code
Clear/Low-E	- Low-E	Clear/Laminated	- Lami.
Bronze/Low-E	- B/ Low-E	Argon/Low-E	- Low-E/Arg

Project:

Architect:

Contractor:

Approved By:

Date:

Specifications:

Skylight shall be factory assembled Model No. _____ EV-G-PVCCM as manufactured by Artistic Skylight Domes Ltd. Vaughan, Ontario. Glazing shall consist of sealed double tempered glass of clear low-E over clear. The skylight incorporates a heavy-duty corrosion resistant chain drive operating motor, pin pivot hinge system and removable insect screen. The skylight shall consist of rigid high-impact extruded vinyl curb frame (superior in thermal conductivity to aluminum) which incorporates a high capacity, 10 degree sloped condensation gutter with drainage to exterior, co-extruded rubber draft seal and a white baked enamel extruded aluminum sash frame, alloy 6063-T5. The retaining cap frame shall be extruded, mill finish (optional baked enamel), 6063-T5 aluminum alloy with heliarc welded corners. Control options include wall mounted switch and/or remote control with rain sensor.

