


Insulating glazing units conform to and exceed test requirements of CAN/CGSG-12.8-M90 and IGMAC certification program.

Skylights are suitable for use on flat roofs only. Designed for mounting on 3"(75mm) or 4"(102mm) curbs with flashing (by others), The flexible design makes it easy to achieve larger daylight openings.

Custom sizes are available upon request



Model G-P-CF-FF Available Sizes				Project:
Model #	Outside Curb Dimensions		Glazing Type	QTY
G-P-CF-FF-42	40" x 40" (1016mm x 1016 mm)			
G-P-CF-FF-52	49½" x 49½" (1251mm x 1251 mm)			
G-P-CF-FF-60	58" x 58" (1473mm x 1473 mm)			
G-P-CF-FF-72	70" x 70" (1778mm x 1778 mm)			
G-P-CF-FF-96	92½" x 92½" (2350mm x 2350mm)			
G-P-CF-FF CUST.				
G-P-CF-FF CUST.				
Glass Glazing Available				Contractor:
Glass Glazing	Colour Code	Glass Glazing	Colour Code	Architect:
Clear/Low-E	- Low-E	Clear/Laminated	- Lami.	Approved By:
Bronze/Low-E	- B/Low-E	Argon/Low-E	- Low-E/Arg	Date:

Specifications:

Skylight shall be factory assembled Model No. _____ G-P-CF-FF as manufactured by Artistic Skylight Domes Ltd. Vaughan, Ontario. Glazing shall consist of sealed dual tempered glass of clear low-E over clear. The skylight shall consist of corrosion resistant extruded aluminum curb frame, 6063-T5 alloy, with heliarc welded corners. The skylight curb frame shall have an extruded aluminum vinyl thermal break, with high capacity, sloped condensation gutter and drainage to exterior. The retaining cap frame shall be extruded, mill finish, 6063-T5 aluminum alloy with heliarc welded corners. Ridge shall consist of double 3" (rafter of single 3") mill finish extruded aluminum channel and pressure plate of 6063-T5 alloy, with keyed in place Santoprene gaskets. Rafters to be at 4' spacing. Options include painted, anodized or powder coated finishes on aluminum.

