

Insulating glazing units conform to and exceed test requirements of CAN/CGSG-12.8-M90 and IGMAC certification program.

Skylights designed to be installed on shingled roofs with minimum 3:12 pitch. These skylights mount directly over roof opening and require no curbs or metal flashings.

- Underlayment required for proper installation.
- Custom sizes are available upon request



Model GV-PVCSR Available Sizes			
Model #	B x B Dimensions	Glass Glazing Type	QTY
GV-PVCSR 2828	22 1/4" x 22 1/4" (565mm x 565mm)		
GV-PVCSR 2836	22 1/4" x 30 1/4" (565mm x 768mm)		
GV-PVCSR 2852	22 1/4" x 46 1/4" (565mm x 1175mm)		
GV-PVCSR 2860	22 1/4" x 55" (565mm x 1397mm)		
GV-PVCSR 2876	22 1/4" x 69 1/2" (565mm x 1765mm)		
GV-PVCSR 3636	30 1/4" x 30 1/4" (768mm x 768mm)		
GV-PVCSR 3642	30 1/4" x 37" (768mm x 940mm)		
GV-PVCSR 3652	30 1/4" x 46 1/4" (768mm x 1175mm)		
GV-PVCSR 3660	30 1/4" x 55" (768mm x 1397mm)		
GV-PVCSR 4242	37" x 37" (940mm x 940mm)		
GV-PVCSR 4252	37" x 46 1/4" (940mm x 1175mm)		
GV-PVCSR 5252	46 1/4" x 46 1/4" (1175mm x 1175mm)		
GV-PVCSR CUST.			
GV-PVCSR CUST.			
Glass Glazing Available			
Glass Glazing	Colour Code	Glass Glazing	Colour Code
Clear/Low-E	- Low-E	Clear/Laminated	- Lami.
Bronze/Low-E	- B/Low-E	Argon/Low-E	- Low-E/Arg
Project:		Architect:	
Contractor:		Approved By:	
		Date:	

**Specifications:**

Skylight shall be factory assembled Model No. \_\_\_\_\_ GV-PVCSR as Manufactured by Artistic Skylight Domes Ltd., Etobicoke, Ontario. Glazing shall consist of, sealed dual tempered glass of clear low-E over clear. The skylight incorporates a heavy duty corrosion resistant chain drive operating mechanism, pin pivot hinge system and removable insect screen. The skylight shall consist of rigid high-impact extruded vinyl base (superior in thermal conductivity to aluminum) which incorporates a high capacity, 18 degree sloped condensation gutter with drainage to exterior, co-extruded rubber draft seal, and 3" (76mm) mounting flange with a white baked enamel extruded aluminum sash frame, alloy 6063-T5. The retaining cap frame shall be extruded, mill finish (optional baked enamel), 6063-T5 aluminum alloy with heliarc welded corners. An optional telescoping pole-hook or electric motorized system are available.

