


## NOTES:

- FRAME MUST BE INSTALLED AT TOP LEVEL OF FINISHED FLOOR COVERING MATERIAL (DO NOT EMBED JAMB IN FLOOR).
- MINIMUM LOCK BACKSET REQUIRED OF 3 3/4".
- FRAME TO BE PREPARED FOR CAM-LIFT HINGES. HINGES SUPPLIED LOOSE BY AMBICO.
- ACOUSTIC SEALS DIMINISH THE FRAME CLEAR OPENING SIZE AS FOLLOWS:
  REBATE WIDTH LESS 3 1/16" = CLEAR OPENING WIDTH OF FRAME.
  REBATE HEIGHT LESS 1 17/32" = CLEAR OPENING HEIGHT OF FRAME.

## LEGEND:

- 1. 1/4" HIGH ACOUSTIC THRESHOLD.
- 2. CASE OPEN BASE FRAME.
- 3. PLANTED STOP FIXED TO CASE OPEN BASE FRAME WITH COUNTERSUNK SCREWS.
- 4. ACOUSTIC PERIMETER SEALS TO BE FITTED AND FASTENED TO JAMBS AND HEAD ON SITE BY INSTALLER.
- 5. ACOUSTIC NEOPRENE SEPTUM TO EXTEND BENEATH PLANTED STOP AND CLAMPED TO FRAME FACE WITH ANGLE.



**DETAIL** "A" 6" = 1'-0"



DRAWING TITLE:

ACOUSTIC STEEL PAIRED FRAME AND PERIMETER SEALS FOR WOOD DOORS STC 55 - NON-FIRE RATED

DATE:	2020/08/19
DRAWN BY:	B. NEIL
REVISION:	4