


GUIDE DIMENSIONS					BETWEEN JAMB OPENING DEDUCTIONS - THEORETICAL 'NEW' OPENING		
GUIDE TYPE	A'	B'	C'	D'	E'		
2	5. 7/8"	3. 3/16"	4"	2. 9/16"	1. 1/4"	2	12"
3	6. 3/8"	3. 9/16"	4. 3/8"	2. 15/16"	1. 1/4"	3	12"
4	6. 3/4"	3. 15/16"	4. 3/4"	2. 3/4"	1. 1/4"	4	12. 3/4"
2(W/L)	6. 3/8"	3. 3/16"	4"	2. 9/16"	1. 1/2"	2(W/L)	12. 3/4"
3(W/L)	6. 3/8"	3. 9/16"	4. 3/8"	2. 15/16"	1. 1/2"	3(W/L)	12. 3/4"
4(W/L)	6. 3/4"	3. 15/16"	4. 3/4"	2. 3/4"	1. 1/2"	4(W/L)	13. 1/2"
5(W/L)	6. 3/4"	4"	4. 3/4"	2. 3/4"	1. 1/2"	5(W/L)	13. 1/2"
6(W/L)	8. 3/4"	6. 1/4"	7. 1/4"	3. 1/2"	1. 1/2"	6(W/L)	17. 1/2"

- GENERAL NOTES**
- SLATS/HOOD: SELECT FINISH OPTION BELOW:
- GALVANIZED ONLY
  - GRAY POLYESTER TOP COAT
  - WHITE POLYESTER TOP COAT
- OTHER SURFACES:
- SHOP COAT BLACK PRIMER
- OPERATION:
- RIGHT HAND SHOWN, LEFT HAND OPPOSITE
- GUIDES:
- STRUCTURAL STEEL ANGLES OF 3/16" MINIMUM THICKNESS
- BOTTOM BAR:
- TWO 2"x2"x1/8" STEEL ANGLES WITH PVC BULB ASTRAGAL
  - TWO 2"x1-1/2"x1/8" GALVANIZED ANGLES WITH PVC BULB ASTRAGAL



NOTE: ADD 'Z' TO 'X' TO ACHIEVE OVERALL HEADROOM REQUIREMENTS

MRK.	QTY.	OPENING SIZE		OPERATION	R.H.	CLEARANCES		OPTION	PROJECT:	ARCHITECT:	CONTRACTOR:	DISTRIBUTOR:	DATE:	SHEET:	OF:	BY:	REF.#	400 SERIES-BETWEEN JAMB-WITH GH MOTOR	
		WIDTH 'W'	HEIGHT 'H'			L.H.	'X'+2'												'V'

Asta Door Corporation is not responsible for the use of improper installation procedures, structural supports as well as field inspection prior to manufacturing and installation.

APPROVAL SIGNATURE: \_\_\_\_\_ DATE: \_\_\_\_\_

4255 McEver Industrial Dr.  
Acworth, GA 30101  
PH:(770) 924-2600  
Fax:(770) 974-1455  
www.astadoor.com