

Model E-V-PVCCM

Dome Venting Curb Mount Skylight (slope roof detail)

Artistic Skylights conform to and exceed test requirements of the following criteria:
 CAN/CGSB 63.14-M89 (1989) (Plastic Skylights): AAMA / WDMA / CSA 101 / IS.2 / A440
 (2008) (NAFS North American Fenestration Standard / Specification for Windows, Doors and
 Skylights): CSA A440.2 (2009) (Fenestration Energy Performance)

Skylights are suitable for use on all types of slope roofs. Designed for mounting on 1½"
 (38mm) curbs with flashing (by others), these units provide excellent performance in all
 geographic locations.

- Flashing kits available for asphalt shingle roofs
- Custom sizes are available upon request
- Custom applications available

Model E-V-PVCCM Available Sizes				
Model #	B x B Dimensions	Dome Color	Flashing Kit y/n	QTY
EV-PVCCM 2828	22¼" x 22¼" (565mm x 565mm)			
EV-PVCCM 2836	22¼" x 30¼" (565mm x 768mm)			
EV-PVCCM 2852	22¼" x 46¼" (565mm x 1175mm)			
EV-PVCCM 2860	22¼" x 55" (565mm x 1397mm)			
EV-PVCCM 2876	22¼" x 69½" (565mm x 1765mm)			
EV-PVCCM 3636	30¼" x 30¼" (768mm x 768mm)			
EV-PVCCM 3642	30¼" x 37" (768mm x 940mm)			
EV-PVCCM 3652	30¼" x 46¼" (768mm x 1175mm)			
EV-PVCCM 3660	30¼" x 55" (768mm x 1397mm)			
EV-PVCCM 3676	30¼" x 69½" (768mm x 1765mm)			
EV-PVCCM 4242	37" x 37" (940mm x 940mm)			
EV-PVCCM 4252	37" x 46¼" (940mm x 1175mm)			
EV-PVCCM 5252	46¼" x 46¼" (1175mm x 1175mm)			
EV-PVCCM CUST.				

Dome Colors Available			
Dome Color	Colour Code	Dome Color	Colour Code
Clear	- C	White	- W
Bronze	- B	Grey	- G

Project:		Architect:
Contractor:	Approved By:	Date:

Specifications:

Skylight shall be factory assembled Model No. _____ EV-PVCCM as manufactured by Artistic Skylight Domes Ltd. Vaughan, Ontario. Glazing shall consist of, sealed double acrylic domes (or sealed triple domes) of clear, white, bronze, or grey. The skylight incorporates a heavy-duty corrosion resistant chain drive operating motor, pin pivot hinge system and removable insect screen. The skylight shall consist of rigid high-impact extruded vinyl curb frame (superior in thermal conductivity to aluminum) which incorporates a high capacity, 10 degree sloped condensation gutter with drainage to exterior, co-extruded rubber draft seal and a white baked enamel extruded aluminum sash frame, alloy 6063-T5. The retaining cap frame shall be extruded, mill finish (optional baked enamel), 6063-T5 aluminum alloy with heliarc welded corners. Control options include wall mounted switch and/or remote control with rain sensor.

