




SLP-10

Low-Profile Electrical Box

Starnet Modular Cable System



Physical Data

- Dimensions of flange $11\frac{1}{2}$ " sq. Dimension of box 10" sq. (Req's. min. 10 ⅓" sq. cutout)
 • Height of box - Fits into ASM
- 40 mm FFH Low-Profile Floor System
- Load rating of lid 1,000 lbf (4448 N)

Electrical Data

- Rated at 20 amp/120V AC
- Plug-in modular simplex receptacles
- Four simplex receptacles provided
- Boxes can be "daisy-chained" together using plug-in modular power-to-power cables
- Comes standard with 12" long Whip **End Extender Cable**

Features

- Available with up to four 20A simplex receptacles
- Lid hinges open or lifts off
- Lid is recessed to accept carpet/tile insert
- Powder coat epoxy paint finish (Available in black color only)
- Welded heavy gauge steel construction
- · 3 openings on each side for Keystone jack couplers



NOTE: Cut sheet drawing and information are subject to change without prior notice.