


NOTES:

1. THIS DETAIL IS APPLICABLE TO OTHER SHAPES, E.G. ROUND/SQUARE TUBES ALSO.
2. FLASHING IS APPLIED TO SMOOTH, SOUND, DRY SUBSTRATES, FREE OF OILS, RUST OR ANY CONTAMINATIONS.
3. IN COLDER TEMPERATURES, A HEAT GUN MUST BE USED WHEN FORMING PRESSURE-SENSITIVE ELASTOFORM OR UNCURED FLASHING.



NOTE:
ON PVC PIPES / PVC SUBSTRATES, ACHIEVE AN ABRADED SURFACE BY GRINDING WITH COARSE SANDPAPER OR POWERED WIRE BRUSH TO ENHANCE THE ADHESION.

MAGNIFIED PVC SURFACE

DIMENSIONS		mm	
(A)	1/2"	13	MIN.
(B)	1"	25	MIN.

PENETRATION DETAIL

5.2

SPF SPRAY POLYURETHANE FOAM
ccSPF CLOSED CELL SPRAY POLYURETHANE FOAM
c.i. CONTINUOUS INSULATION
LGMF LIGHT GAUGE METAL FRAME

0 NOTE(S)
SPRAYED POLYURETHANE FOAM

For additional information, refer to Specifications