



Innovative Products

2395 West 4th Avenue Denver, CO 80223 USA
 Phone 303.892.0400 Toll Free 800.333.4234 Fax 303.825.5988
 EMail info@BisonIP.com Web www.BisonIP.com

Get CEU Credits, Details & Specifications online at BisonIP.com

SCREWJACK
 Adjustable Deck Supports


"T" METHOD: DETERMINE CAVITY HEIGHT AT ALL THRESHOLDS, DRAINS AND HIGH POINTS. DEDUCT THE THICKNESS OF THE DECKING MATERIAL FROM THE MEASURED DISTANCE BETWEEN THE TOP OF THE MEMBRANE AND THE TOP OF THE DECKING MATERIAL TO DETERMINE THE PEDESTAL HEIGHT AND MODELS NEEDED FOR EACH LOCATION. USE A "LASER LEVEL" TO MARK THE TOP OF PEDESTAL ELEVATION AROUND THE DECK. PLAN PAVER/PEDESTAL LAYOUT PATTERN BEFORE STARTING, BY MARKING GUIDELINES ON THE ROOF IF NEEDED. USING THE GUIDELINES INSTALL A "T" SHAPED PORTION OF THE NEW DECK STARTING FROM THE THRESHOLD (OR HIGH POINT). DECKING ON BOTH ROWS OF THE "T" SHOULD BE ADJUSTED TO THE CORRECT HEIGHT AND LEVELED BEFORE PROCEEDING. INSTALLATION ON ALL SIDES OF THE "T" CAN THEN PROCEED AT THE SAME TIME.

ACRONYM	MEANING
LP	LOW POINT OF ROOF
HP	HIGH POINT OF ROOF

REMOVE TABS AS NECESSARY ON PERIMETER PEDESTALS (TYP)

START AT THE HIGH POINT OR THRESHOLD WITH WHOLE PAVERS (IF POSSIBLE)

MAXIMUM 1/8" GAP AT PERIMETER (TYP)



GENERAL NOTES: APPLY TO ALL OF THE ABOVE PRODUCTS

1. INSTALLATION MUST BE COMPLETED IN ACCORDANCE WITH BISON INNOVATIVE PRODUCTS SPECIFICATIONS.
2. DRAWINGS NOT TO SCALE.
3. CONTRACTOR'S NOTE: FOR PRODUCT AND COMPANY INFORMATION VISIT www.BisonIP.com

2 **STARTING INSTALLATION**
 USING "T" INSTALLATION METHOD