



- NOTES:** UNLESS OTHERWISE SPECIFIED
1. DIMENSIONS ARE IN INCHES (MM).
 2. MACHINED SURFACES TO BE 63 μ IN MAX.
 3. DO NOT SCALE DRAWING.
 4. PART TO BE FREE OF BURRS AND SHARP EDGES.
 5. ALL MATERIAL TO BE CLEAN, DEGREASED AND FREE OF ALL IMPURITIES.
 6. ANY CHANGE MUST BE AUTHORIZED BY AN SC&R ENGINEER.

MATERIAL TYPE: 316 SS

VENDOR ID:

| REV | DATE | DESCRIPTION OF CHANGE | REVISIONS | | | ECH | BY | APPV |
|--------|----------------------------|---|--|--|--|-----|--------------------|------|
| SC & R | Stainless Cable S. Railing | JX 4.00 JXX 3.005 ANGULAR 44.5° FRACTIONAL 1/2 | TOLERANCES HOLE PRELIMINARY SPECIFIED | SEE DRAWING FOR THE NUMBER OF HOLES AND SPACING AND IN PARTICULAR CASES REFER TO THE DRAWING FOR THE NUMBER OF HOLES AND SPACING. SEE THE DRAWING FOR THE NUMBER OF HOLES AND SPACING. | | | Stainless 2" Elbow | |
| 05 | 1/8/2011 | | | 05-160-01 | | | SHEET 1 OF 1 | |