



NOTES: UNLESS OTHERWISE SPECIFIED

1. DIMENSIONS ARE IN INCHES (MM).
2. MACHINED SURFACES TO BE 63 μ IN MAX.
3. DO NOT SCALE DRAWING.
4. PART TO BE FREE OF BURRS AND SHARP EDGES.
5. ALL MATERIAL TO BE CLEAN, DEGREASED AND FREE OF ALL IMPURITIES.
6. ANY CHANGE MUST BE AUTHORIZED BY AN SC&R ENGINEER.

MATERIAL TYPE: 316 SS

VENDOR ID:

REV	DATE	DESCRIPTION OF CHANGE	REVISIONS			ECN	BY	APPR	
			SC & R Stainless Cable S. Railing	XX ±.01 XXX ±.005 FRACTIONAL 1/32	TOLERANCES UNLESS OTHERWISE SPECIFIED	THIS DRAWING IS THE PROPERTY OF SC&R RAILING. IT IS TO BE KEPT IN CONFIDENTIALITY AND NOT TO BE REPRODUCED, COPIED, OR OTHERWISE USED FOR ANY OTHER PURPOSE WITHOUT THE WRITTEN PERMISSION OF SC&R RAILING.	Part: Stainless 2" Flush Tee		
001	1/8/2011	ISSUED	GH						05-180-01 SHEET 1 OF 1