



NOTES: UNLESS OTHERWISE SPECIFIED

1. DIMENSIONS ARE IN INCHES (MM).
2. MACHINED SURFACES TO BE 63 μ IN MAX.
3. DO NOT SCALE DRAWING.
4. PART TO BE FREE OF BURRS AND SHARP EDGES.
5. ALL MATERIAL TO BE CLEAN, DEGREASED AND FREE OF ALL IMPURITIES.
6. ANY CHANGE MUST BE AUTHORIZED BY AN SC&R ENGINEER.

MATERIAL TYPE:	316 SS
VENDOR ID:	

REV	DATE	DESCRIPTION OF CHANGE	ECN	BY	APPV
REVISIONS					
	Stainless Cable S. Railing	XX 4.00 XXX 3.005 ANGLE 45° FRACTIONAL 1/2	TOLERANCES DECIMAL FRACTIONS UNLESS OTHERWISE SPECIFIED	THIS DRAWING IS THE PROPERTY OF SC&R ENGINEERING AND IS NOT TO BE REPRODUCED OR COPIED IN ANY MANNER WITHOUT THE WRITTEN PERMISSION OF SC&R ENGINEERING.	
	Part Name: Stainless 2" End Wall Return		Part No: 05-190-01		SHEET 1 OF 1
Drawn By: GH	Date: 1/8/2011	Project:			