



- NOTES : UNLESS OTHERWISE SPECIFIED
1. DIMENSIONS ARE IN MM .
  2. MACHINED SURFACES TO BE 63 $\mu$ IN MAX.
  3. DO NOT SCALE DRAWING.
  4. PART TO BE FREE OF BURRS AND SHARP EDGES.
  5. ALL MATERIAL TO BE CLEAN, DEGREASED AND FREE OF ALL IMPURITIES.
  6. ANY CHANGE MUST BE AUTHORIZED BY AN SC&R ENGINEER.

MATERIAL TYPE : 316 SS

VENDOR ID:

| REV              | DATE | DESCRIPTION OF CHANGE   | ECN   | BY. | APPR   |
|------------------|------|---|---|-----|--|
| REVISIONS        |      |   |   |     |  |
|                  |      | <b>TOLERANCES</b><br>XX ±.01 UNLESS OTHERWISE SPECIFIED<br>XXX ±.005<br>ANGULAR ±0.5°<br>FRACTIONAL ±1/32 | THIS DRAWING IS THE PROPERTY OF STAINLESS CABLE & RAILING AND IS PROTECTED UNDER COPYRIGHT LAW AS AN UNPUBLISHED WORK. IT MAY NOT BE PUBLISHED, COPIED OR REPRODUCED WITHOUT EXPRESS WRITTEN PERMISSION FROM SC&R |     | <b>TITLE :</b><br>SSQ 2" POST CAP Terminal/Fixed/Flat Saddle |
| <b>DRAWN BY:</b> |      | <b>DATE:</b>  | <b>PROJECT:</b>   |     | <b>DRG NO.</b><br>06-200-01-ASM                              |
|                  |      |   |   |     | <b>SHEET</b><br>1 OF 1                                       |