



## NOTES:

1. REMOVE ALL LEAD AND OTHER FLASHING BEFORE INSTALLING PRESSURE-SENSITIVE ELASTOFORM FLASHING.
2. TEMPERATURE OF PIPE MUST NOT EXCEED 180°F (82°C).
3. HP FASTENERS AND POLYMER SEAM PLATES ARE REQUIRED OVER STEEL DECKS.
4. FOR STRUCTURAL STEEL TUBING GREATER THAN 12" ACROSS USE U-5 DETAILS.




DIMENSIONS		cm	
(A)	1/2"	1.5	
(B)	3"	7.5	
(C)	1"	2.5	
(D)	6"	15	T0
	12"	30	
(E)	12"	30	MAX.



FIELD FABRICATED PIPE WRAP (25/30 YEAR WARRANTIES)

MAXIMUM WARRANTY: 30 YEARS



DETAIL NO.

MF-8B.1

MECHANICALLY FASTENED