



NOTES:

1. ALL OUTSIDE AND INSIDE CORNERS REQUIRE TWO COMPLETE CORNER APPLICATIONS OF PRESSURE-SENSITIVE ELASTOFORM FLASHING AS PER DETAILS U-15D.1 OR U-15G.1.
2. ROOF MEMBRANE SHALL BE LOOSE-LAID OVER THE EXPANSION JOINT SUPPORT OR SPONGE TUBING.
3. WIDTH OF JOINT SHALL BE A MINIMUM OF 3/4" (2cm) AND MAXIMUM 2" (5cm) WHEN CARLISLE EXPANSION JOINT SUPPORT IS USED.
4. USE DETAIL U-2C FOR EPDM MEMBRANE SPLICES AT ANGLE CHANGES.
5. HP FASTENERS AND POLYMER SEAM PLATES ARE REQUIRED ON MECHANICALLY FASTENED SYSTEMS OVER STEEL DECKS.
6. MAXIMUM 6" (15cm) FASTENER SPACING FOR WARRANTY WIND SPEEDS GREATER THAN 90 MPH OR WARRANTIES EXCEEDING 20 YEARS.



DECK-TO-WALL EXPANSION JOINT

MAXIMUM WARRANTY: 30 YEARS



DETAIL NO.

U-3B

THERMOSET UNIVERSAL