



NOTES:

1. PRE-CUT 7" X 9" CORNER OR 9" X 9" PRESSURE SENSITIVE ELASTOFORM.
2. FOR PROJECTS WITH 25 AND 30-YEAR WARRANTIES OR WHEN USING 90-MIL MEMBRANE, INSTALL A 6" T-JOINT COVER PRIOR TO INSTALLING A 12" T-JOINT COVER. SEAL TOP LAYER WITH CONTINUOUS LAP SEALANT. PER DETAIL [U-15D.1](#)
3. A HEAT GUN MUST BE USED WHEN FORMING PRESSURE-SENSITIVE ELASTOFORM FLASHING IN COLDER TEMPERATURES.



INSIDE CORNER WITH CONTINUOUS EPDM WALL FLASHING

MAXIMUM WARRANTY: 30 YEARS



DETAIL NO.

U-15C

THERMOSET UNIVERSAL