



NOTES:

1. REMOVE ALL LEAD AND OTHER FLASHING BEFORE INSTALLING FIELD-FABRICATED FLASHING.
2. TEMPERATURE OF PIPE PENETRATION MUST NOT EXCEED 180°F (82°C).
3. ACCEPTABLE WITH SQUARE OR RECTANGULAR STRUCTURAL TUBING WITH ROUNDED CORNERS UP TO 12" (30cm). USE [DETAIL U-5](#) IF GREATER THAN 12" (30cm).
4. IN COLDER TEMPERATURES, A HEAT GUN MUST BE USED WHEN FORMING PRESSURE-SENSITIVE ELASTOFORM OR CURED FLASHING.
5. ON MECHANICALLY FASTENED ROOFING SYSTEMS. REFER TO [DETAIL MF-8B](#).
6. MEMBRANE SECUREMENT IS REQUIRED AROUND ALL ROUND PIPE PENETRATIONS GREATER THAN 18" (46cm) IN DIAMETER.

DIMENSIONS		cm	
(A)	1/2"	1.5	MIN.
(B)	1"	2.5	MIN.
(C)	3"	7.5	MIN.



FIELD FABRICATED PIPE WRAP

MAXIMUM WARRANTY: 20 YEARS



DETAIL NO.

U-8B

THERMOSET UNIVERSAL