


NOTE:


1. MAXIMUM MEMBRANE THICKNESS GOING OVER THE WATER DAM IS 60-MIL. FOR THICKER MEMBRANES, RUN FIELD SHEET UNDER THE WATER DAM AND STRIP-IN WITH MAXIMUM 60-MIL MEMBRANE.
2. USE [MF-1A](#) FOR MECHANICALLY FASTENED SYSTEMS AND [B-1A](#) FOR BALLASTED SYSTEMS.

AT CORNERS, 6" (15cm) WIDE PRESSURE-SENSITIVE RUSS MUST BE INSTALLED 12" (30cm) MAXIMUM FROM THE BASE OF THE WATER DAM AND EXTEND 36" (90cm) MINIMUM IN EACH DIRECTION.



CORNER REINFORCEMENT

PRESSURE-SENSITIVE T-JOINT COVER AND EPDM PRIMER



MEMBRANE SEAM AT EDGE



CARLISLE SecurEDGE 200

MAXIMUM WARRANTY: 20 YEARS



DETAIL NO.

U-1A

THERMOSET UNIVERSAL