



PRE-MOLDED INSIDE
CORNER BEFORE
INSTALLATION

NOTES:

1. POSITION FASTENING PLATES 6" TO 9" (15 TO 23cm) FROM THE CORNER AND 1/2" TO 1" (1.5 TO 2.5cm) FROM EDGE OF MEMBRANE.
2. APPROXIMATELY 1/8" (0.5cm) DIAMETER BEAD OF CUT-EDGE SEALANT IS REQUIRED ON CUT EDGES OF REINFORCED TPO MEMBRANE.
3. REFER TO CARLISLE SPECIFICATIONS FOR ACCEPTABLE CARLISLE FASTENERS AND PLATES.
4. WHEN USING 60-MIL TPO OR 80-MIL TPO OR PVC MEMBRANE, APPLY A 4-1/2" (11.5cm) DIAMETER "T-JOINT" COVER AT ALL FIELD SPLICE INTERSECTIONS.

DIMENSIONS		cm	
(A)	6"	15	APPROX.
(B)	6"-9"	15-23	
(C)	45-DEGREES APPROX.		



PRE-MOLDED INSIDE CORNER
FLASHING

MAXIMUM WARRANTY: 30 YEARS



DETAIL NO.

U-15A

THERMOPLASTIC UNIVERSAL